

INTERCONNECTS

SERIES 410, 411, 415 • .100" GRID SOLDER TAIL • DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3





FIG. 4

- Series 41X double row strip sockets are on .100" grid
- Various solder tails available: standard length, long for multi-layer boards, very low and ultra low profile. See Mill-Max #1001, #0134, #0501 or #1534 pins. See pages 161, 162 and 165 for details
- Hi-Rel, 4-finger BeCu #12 and #30 contact are rated at 3 amps. See pages 252 and 253 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 410...001	Standard Solder Tail					
	410-XX-2-41-001000 Specify number of pins 04-64						
FIG. 2	Series 411...001	Long Solder Tail					
	411-XX-2-41-001000 Specify number of pins 04-64						
FIG. 3	Series 415...001	Very Low Profile					
	415-XX-2-41-001000 Specify number of pins 04-64						
FIG. 4	Series 415...003	Ultra Low Profile					
	415-XX-2-41-003000 Specify number of pins 04-64						
RoHS - 2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264							
SPECIFY PLATING CODE XX=							
Sleeve (Pin)	11	13	91	93	41	43	47
Contact (Clip)							



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[415-93-272-41-003000](#) [415-93-264-41-001000](#) [415-13-264-41-001000](#) [411-13-264-41-001000](#) [410-93-264-41-001000](#) [410-13-264-41-001000](#) [410-13-216-41-001000](#) [415-43-272-41-003000](#) [415-43-264-41-001000](#) [410-43-264-41-001000](#) [415-13-272-41-003000](#) [410-93-220-41-001000](#) [415-13-224-41-003000](#) [415-13-228-41-003000](#) [415-13-250-41-003000](#) [415-93-214-41-001000](#) [410-13-220-41-001000](#) [4015-0-15-80-30-27-10-0](#) [4015-0-15-15-30-27-10-0](#) [4015-0-15-00-00-00-10-0](#) [4015-0-15-01-30-02-10-0](#) [4015-0-15-80-30-84-10-0](#) [4015-0-15-01-30-27-10-0](#) [410-43-260-61-001000](#) [410-93-262-61-001000](#) [410-43-230-61-001000](#) [410-93-252-61-001000](#) [410-43-218-61-105000](#) [410-13-210-61-001000](#) [410-93-218-61-001000](#) [410-43-240-61-001000](#) [410-43-250-61-001000](#) [410-93-208-61-001000](#) [410-13-222-61-001000](#) [410-13-262-61-001000](#) [410-13-232-61-001000](#) [410-13-252-61-001000](#) [410-43-204-61-105000](#) [410-43-258-61-001000](#) [410-93-242-61-001000](#) [410-43-220-61-001000](#) [410-43-210-41-105000](#) [410-13-242-61-001000](#) [410-43-246-61-105000](#) [410-43-226-61-105000](#) [410-93-232-61-001000](#) [410-93-214-61-001000](#) [410-43-206-61-001000](#) [410-43-236-61-105000](#) [410-13-258-61-001000](#) [410-13-226-41-001000](#) [410-43-216-61-105000](#) [410-93-202-61-001000](#) [410-93-212-61-001000](#) [410-13-238-61-001000](#) [410-91-216-10-002000](#) [410-13-228-61-001000](#) [410-43-252-61-001000](#) [410-43-232-61-001000](#) [410-43-266-61-105000](#) [410-93-222-61-001000](#) [410-13-214-61-001000](#) [410-43-230-61-105000](#) [410-13-236-61-001000](#) [410-13-246-61-001000](#) [410-13-226-61-001000](#) [410-43-228-61-105000](#) [410-43-258-61-105000](#) [410-43-222-61-001000](#) [410-43-240-61-105000](#) [410-13-256-61-001000](#) [410-93-256-61-001000](#) [410-13-218-61-001000](#) [410-43-206-61-105000](#) [410-93-246-61-001000](#) [410-43-238-61-105000](#) [410-43-262-61-105000](#) [410-13-260-61-001000](#) [410-43-264-61-105000](#) [410-93-224-61-001000](#) [410-43-232-61-105000](#) [410-43-212-61-001000](#) [410-43-242-61-105000](#) [410-43-254-61-001000](#) [410-43-250-61-105000](#) [410-93-250-61-001000](#) [410-93-260-61-001000](#) [410-13-208-61-001000](#) [410-43-224-61-001000](#) [410-43-214-61-001000](#) [410-93-230-61-001000](#) [410-43-202-61-001000](#) [410-93-204-61-001000](#) [410-43-254-61-105000](#) [410-93-248-61-001000](#) [410-93-226-61-001000](#) [410-13-250-61-001000](#) [410-43-222-61-105000](#) [410-43-202-61-105000](#) [410-93-228-61-001000](#)