

# PIN RECEPTACLES

FOR 0,81 - 1,17 DIAMETER PINS

<p><b>0359</b> <b>0359-0-15-XX-34-XX-10-0</b> Press-fit in 2,29 mounting hole</p>	<p><b>0358</b> <b>0358-0-15-XX-34-XX-10-0</b> Press-fit in 2,29 mounting hole</p>	<p><b>0360</b> <b>0360-0-15-XX-34-XX-10-0</b> Press-fit in 2,29 mounting hole</p>	<p><b>0343</b> <b>0343-0-15-XX-34-XX-10-0</b> Press-fit in 2,29 mounting hole</p>
<p><b>0356</b> <b>0356-0-15-XX-34-XX-10-0</b> Solder mount in 2,59 min. mounting hole Also available on 24mm wide carrier tape: 1,100 parts per 330mm reel See page 194.11 for Tape &amp; Reel details</p>	<p><b>6659</b> <b>6659-0-15-XX-34-XX-10-0</b> Solder mount in 2,59 min. mounting hole</p>	<p><b>0347</b> <b>0347-0-15-XX-34-XX-10-0</b> Solder mount in 3,05 min. mounting hole</p>	<p><b>0329</b> <b>0329-0-15-XX-34-XX-10-0</b> Solder mount in 1,91 min. mounting hole. "Knock out" bottom</p>
<p><b>0814</b> <b>0814-0-15-XX-34-XX-04-0</b> Solder mount in 2,08 min. mounting hole</p>	<p><b>5059</b> <b>5059-0-15-XX-34-XX-04-0</b> Press-fit in 2,29 mounting hole</p>	<p><b>8360</b> <b>8360-0-15-XX-34-XX-10-0</b> Press-fit in 2,21 mounting hole</p>	<p><b>9359</b> <b>9359-0-15-XX-34-XX-10-0</b> Press-fit in 2,29 mounting hole</p>

## SPECIFICATIONS:

**Shell Material:** Brass Alloy 360, 1/2 Hard

**Contact Material:** Beryllium Copper Alloy 172, HT

**Dimensions:** Millimeters

**Tolerances On:** Lengths: ±0,13

Diameters: ±0,051

Angles: ±2°



**ORDER CODE:** XXXX - X - XX - XX - 34 - XX - XX - 0

**BASIC PART #**

**SPECIFY SHELL FINISH:**

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◆ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◆ 15 0,25µm GOLD OVER NICKEL (RoHS)

**SPECIFY CONTACT FINISH:**

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◆ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◆ 27 0,76µm GOLD OVER NICKEL (RoHS)

**SELECT CONTACT:**

**#34 CONTACT (DATA ON PAGE 258)**

(For alternate contact choices, see group E on page 248)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mill-Max:](#)

[0358-0-15-15-34-27-10-0](#)