



2297



Basic Part Number	# of Wraps	Length A
2297-2	2	.370
2297-3	3	.430

2297-X-17-XX-16-XX-02-0
Press-fit in .067 mounting hole


0280



Basic Part Number	# of Wraps	Length A
0280-2	2	.360
0280-3	3	.510

0280-X-17-XX-06-XX-02-0
Press-fit in .081 mounting hole

0281



0281-3-17-XX-06-XX-02-0
Press-fit in .080 mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 17 - XX - X6 - XX - 02 - 0

BASIC PART # _____

SPECIFY SHELL FINISH:

01 200μ" TIN/LEAD OVER NICKEL

80 200μ" TIN OVER NICKEL ◇

15 10μ" GOLD OVER NICKEL ◇

SPECIFY CONTACT FINISH:

01 200μ" TIN/LEAD OVER NICKEL

80 200μ" TIN OVER NICKEL ◇

14 30μ" GOLD OVER NICKEL ◇

SELECT CONTACT

#06 or #16 CONTACT (DATA ON PAGE 210)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[2297-3-17-01-16-14-02-0](#) [0280-3-17-80-06-14-02-0](#) [2297-2-17-01-16-14-02-0](#) [2297-3-17-80-16-14-02-0](#) [0280-2-17-80-06-14-02-0](#) [0280-3-17-01-06-14-02-0](#) [2297-2-17-80-16-14-02-0](#) [0281-3-17-80-06-14-02-0](#) [0280-2-17-01-06-14-02-0](#) [0281-3-17-15-06-14-02-0](#) [0280-2-17-15-06-14-02-0](#) [2297-3-17-15-16-14-02-0](#)