




0394

0394-0-15-XX-07-XX-10-0


Solder mount in .120 min.
mounting hole

0393

0393-0-15-XX-07-XX-10-0


Solder mount in .144 min.
mounting hole

0391

0391-0-15-XX-07-XX-10-0


Solder mount in .159 min.
mounting hole

9016

9016-0-15-XX-07-XX-10-0


Press-fit in .131 mounting hole

0493

0493-0-15-XX-07-XX-10-0


Press-fit in .144 mounting hole

0490

0490-0-15-XX-07-XX-04-0


Press-fit in .144 mounting hole

0616

0616-0-18-XX-07-XX-10-0


Press-fit in .144 mounting hole

0387

0387-0-15-XX-07-XX-04-0


Solder mount in .063 min.
mounting hole

0370

0370-0-19-XX-07-XX-10-0


#18 Gage crimp barrel

4040

4040-0-19-XX-07-XX-10-0

Wire Termination

0491

0491-0-19-XX-07-XX-04-0

For use in stackable
patch cords

9214

9214-0-15-XX-07-XX-10-0

Solder mount in .083 min.
mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - 0 - 1X - XX - 07 - XX - XX - 0

BASIC PART #
SPECIFY SHELL FINISH:
01 200μ" TIN/LEAD OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
01 200μ" TIN/LEAD OVER NICKEL
14 10μ" GOLD OVER NICKEL
27 30μ" GOLD OVER NICKEL

SELECT CONTACT

#07 CONTACT (DATA ON PAGE 214)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0391-0-15-01-07-14-10-0](#) [0393-0-15-01-07-14-10-0](#) [0493-0-15-01-07-14-10-0](#) [4040-0-19-01-07-14-10-0](#)