

0364	0363	0365	0366
0364-0-15-XX-13-XX-10-0 Solder mount in .100 min. mounting hole	0363-0-15-XX-23-XX-10-0 Solder mount in .102 min. mounting hole	0365-0-15-XX-23-XX-10-0 Hex press-fit in .105 plated thru hole	0366-0-15-XX-13-XX-10-0 Press-fit in .109 mounting hole
0372	0362	0367	9324
0372-0-15-XX-13-XX-10-0 Solder mount in .102 min. mounting hole	0362-0-15-XX-X3-XX-10-0 Solder mount in .102 min. mounting hole	0367-0-15-XX-23-XX-10-0 Square press-fit in .040 plated thru hole	9324-0-15-XX-23-XX-04-0 Press-fit in .106 mounting hole
0492	0381	4034	3044
0492-0-15-XX-13-XX-04-0 Press-fit in .106 mounting hole	0381-0-15-XX-23-XX-10-0 Press-fit in .104 mounting hole	4034-0-15-XX-23-XX-04-0 Press-fit in .109 mounting hole	3044-0-15-XX-23-XX-04-0 Solder mount in .104 min. mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 15 - XX - X3 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:
01 200μ" TIN/LEAD OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:
01 200μ" TIN/LEAD OVER NICKEL
14 10μ" GOLD OVER NICKEL
27 30μ" GOLD OVER NICKEL

SELECT CONTACT

#13 or #23 CONTACT (DATA ON PAGE 214)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0492-0-15-01-13-14-04-0](#) [0362-0-15-01-23-14-10-0](#) [0362-0-15-01-13-14-10-0](#) [0381-0-15-01-23-14-10-0](#) [0381-0-15-15-23-14-10-0](#)