







- All DIP sockets accept 0,38 - 0,64mm dia. and standard IC leads.
- Lubricated contacts also available. (See page 96 for specs.)
- Hi-Rel, 4-finger BeCu #30 clip rated at 3 amps. See page 208 for details.
- Uses Mill-Max #1001 pin. See page 134 for details.



Total number of pins				Quantity per tube	Ordering Information	
	A	B	C			
10	12,6	5,08	7,6	40		110-XX-210-41-001000
4	5,0	7,62	10,1	102		110-XX-304-41-001000
6	7,6	7,62	10,1	67		110-XX-306-41-001000
8	10,1	7,62	10,1	50		110-XX-308-41-001000
10	12,6	7,62	10,1	40		110-XX-310-41-001000
14	17,7	7,62	10,1	28		110-XX-314-41-001000
16	20,3	7,62	10,1	25		110-XX-316-41-001000
18	22,8	7,62	10,1	22		110-XX-318-41-001000
20	25,3	7,62	10,1	20		110-XX-320-41-001000
22	27,8	7,62	10,1	18		110-XX-322-41-001000
24	30,4	7,62	10,1	16		110-XX-324-41-001000
28	35,5	7,62	10,1	14		110-XX-328-41-001000
20	25,4	10,16	12,7	20		110-XX-420-41-001000
22	27,8	10,16	12,7	18		110-XX-422-41-001000
24	30,4	10,16	12,7	16		110-XX-424-41-001000
28	35,5	10,16	12,7	14		110-XX-428-41-001000
32	40,6	10,16	12,7	12		110-XX-432-41-001000
24	30,5	15,24	17,7	16		110-XX-624-41-001000
28	35,5	15,24	17,7	14		110-XX-628-41-001000
32	40,6	15,24	17,7	12		110-XX-632-41-001000
36	45,7	15,24	17,7	11		110-XX-636-41-001000
40	50,8	15,24	17,7	10		110-XX-640-41-001000
42	53,3	15,24	17,7	9	110-XX-642-41-001000	
48	60,9	15,24	17,7	8	110-XX-648-41-001000	
50	63,5	15,24	17,7	8	110-XX-650-41-001000	
52	66,0	15,24	17,7	7	110-XX-652-41-001000	
50	63,5	22,86	25,3	8		110-XX-950-41-001000
52	66,0	22,86	25,3	7		110-XX-952-41-001000
64	81,2	22,86	25,3	6		110-XX-964-41-001000

For Lubricated Contacts, change part number from 110-XX-XXX-41-001000 to 110-99-XXX-41-361000 (To be used with "99" plating code only)

For Lubricated Contacts, change part number from 110-XX-XXX-41-001000 to 110-99-XXX-41-361000 (To be used with "99" plating code only)

SPECIFY PLATING CODE XX=	13	91	93	99	41	43	44
Sleeve (Pin)	0,25µm Au	5,08µm Sn/Pb	5,08µm Sn/Pb	5,08µm Sn/Pb	5,08µm Sn	5,08µm Sn	5,08µm Sn
Contact (Clip)	0,76µm Au	0,25µm Au	0,76µm Au	5,08µm Sn/Pb	0,25µm Au	0,76µm Au	5,08µm Sn

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[110-13-314-41-001100](#)