



■ Features :

- 2:1 wide input range
- 4:1 wide input range(option)
- 1000VDC I/O isolation
- 3000VDC I/O isolation(option)
- Built-in EMI filter
- Protections: Short circuit / Overload
- Cooling by free air convection
- Six-sided shield metal case
- 100% burn-in test
- Low cost / High reliability
- Approvals: FCC / CE
- 2 years warranty




SPECIFICATION

ORDER NO.		SKA15A-033	SKA15B-033	SKA15C-033	SKA15A-05	SKA15B-05	SKA15C-05	SKA15A-12	SKA15B-12	SKA15C-12	SKA15A-15	SKA15B-15	SKA15C-15	
OUTPUT	DC VOLTAGE	3.3V			5V			12V			15V			
	CURRENT RANGE	300 ~ 3000mA			300 ~ 3000mA			125 ~ 1250mA			100 ~ 1000mA			
	RATED POWER	9.9W			15W									
	RIPPLE & NOISE (max.) Note.2	50mVp-p			50mVp-p			60mVp-p			60mVp-p			
	LINE REGULATION Note.3	±0.2%												
	LOAD REGULATION Note.4	±0.5%												
	VOLTAGE ACCURACY	±2.0%												
	SWITCHING FREQUENCY	150KHz min.												
INPUT	VOLTAGE RANGE	A: 9 ~ 18VDC B: 18 ~ 36VDC C: 36 ~ 72VDC												
	EFFICIENCY (Typ.)	76%	76%	76%	78%	78%	80%	82%	80%	82%	82%	80%	82%	
	DC CURRENT	Full load	A: 1700mA B: 800mA C: 400mA											
		No load	A: 20mA B: 30mA C: 15mA											
	FILTER	Pi network												
	PROTECTION	Fuse recommended												
PROTECTION (Note. 5)	OVER CURRENT	110% ~ 250% rated output power												
		Protection type : Hiccup mode, recovers automatically after fault condition is removed												
	SHORT CIRCUIT	All output equipped with short circuit												
		Protection type : Hiccup mode, recovers automatically after fault condition is removed												
ENVIRONMENT	WORKING TEMP.	-40 ~ +71℃ (Refer to output load derating curve)												
	WORKING HUMIDITY	20% ~ 90% RH non-condensing												
	STORAGE TEMP., HUMIDITY	-40 ~ +105℃, 10 ~ 95% RH												
	TEMP. COEFFICIENT	±0.03% / °C (0 ~ 50℃)												
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes												
SAFETY & EMC	WITHSTAND VOLTAGE	I/P-O/P:1KVDC												
	ISOLATION RESISTANCE	I/P-O/P: 100M Ohms / 500VDC / 25℃ / 70% RH												
	EMC EMISSION	Compliance to EN55022 Class B, FCC part 15 Class B												
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8, light industry level, criteria A												
OTHERS	MTBF	300Khrs min. MIL-HDBK-217F(25℃)												
	DIMENSION	50.8*25.4*11.27 mm or 2"*1"*0.44" inch (L*W*H)												
	WEIGHT	32g												

■ Mechanical Specification


Unit:mm(inch)



■ Pin Configuration

Pin No.	Output
1	+Vin
2	-Vin
3	+Vout
4	No Pin
5	-Vout

■ Derating Curve



NOTE

- 1.All parameters are specified at normal input, rated load, 25°C 70% RH ambient.
- 2.Ripple & noise are measured at 20MHz by using a 12" twisted pair terminated with a 0.1uf & 47uf capacitor.
- 3.Line regulation is measured from low line to high line at rated load.
- 4.Load regulation is measured from 10% to 100% rated load.
- 5.Please prevent the converter from operating in overload or short circuit condition for more than 30 seconds.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[MEAN WELL:](#)

[SKA-15A-05](#)