







**Fig. 1**



**Fig. 2**




**Fig. 3**



**Fig. 4**

- Series 41X double row strip sockets are on 2,54 grid.
- Various solder tails available: standard length, long for multi-layer boards, very low and ultra low profile. Using Mill-Max #1001, 0134, 0501 or 1534 pins (See pages 132, 133, 136) for details.
- Hi-Rel, 4-finger BeCu #12 & #30 contacts are rated at 3 amps. See page 218 for details.
- Insulators are high temp. thermoplastic.



## Ordering Information

| Fig. 1 | Series 410...001     | Standard Solder Tail      |
|--------|----------------------|---------------------------|
|        | 410-XX-2_ -41-001000 | Specify # of pins → 02-64 |
| Fig. 2 | Series 411...001     | Long Solder Tail          |
|        | 411-13-2_ -41-001000 | Specify # of pins → 02-64 |
| Fig. 3 | Series 415...001     | Very Low Profile          |
|        | 415-XX-2_ -41-001000 | Specify # of pins → 02-64 |
| Fig. 4 | Series 415...003     | Ultra Low Profile         |
|        | 415-XX-2_ -41-003000 | Specify # of pins → 02-72 |

For Electrical, Mechanical & Environmental Data, See pg. 4

XX=Plating Code See Below

For RoHS compliance select ◇ plating code.

| SPECIFY PLATING CODE XX= | 13◇       | 93           | 43◇       |
|--------------------------|-----------|--------------|-----------|
| Sleeve (Pin)             | 0,25µm Au | 5,08µm Sn/Pb | 5,08µm Sn |
| Contact (Clip)           | 0,76µm Au | 0,76µm Au    | 0,76µm Au |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[415-93-272-41-003000](#) [415-43-272-41-003000](#) [415-13-272-41-003000](#) [411-13-202-41-001000](#) [410-93-202-41-001000](#) [415-13-202-41-001000](#) [415-93-202-41-003000](#)