


1030 ⇒ 1032



103X-X-05-XX-00-00-01-0
Press-fit in .057 mounting hole


Basic Part Number	# of Wraps	Wrapost Length A
1032-1	1	.260
1031-2	2	.360
1030-3	3	.500

1216




1216-0-05-XX-00-00-01-0
Press-fit in .056 mounting hole

1095




1095-0-05-XX-00-00-01-0
Swage mount in .094 hole
For .062 thick board

1214




1214-0-05-XX-00-00-01-0
Press-fit in .059 mounting hole

1212




1212-0-05-XX-00-00-01-0
Press-fit in .061 mounting hole

1213



1213-0-05-XX-00-00-01-0
Press-fit in .061 mounting hole

0318



0318-3-05-XX-00-00-01-0
Press-fit in .057 mounting hole

1302



1302-0-05-XX-00-00-01-0
Press-fit in .057 mounting hole

1097



1097-0-05-XX-00-00-01-0
Swage mount in .094 hole
for .062 thick board

SPECIFICATIONS

PIN MATERIAL:
Brass Alloy 360, 1/2 Hard
Swage pins are annealed

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 05 - XX - 00 - 00 - 01 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 15 10μ" GOLD OVER NICKEL (RoHS)
- ◇ 21 20μ" GOLD OVER NICKEL (RoHS)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[1095-0-05-80-00-00-01-0](#) [1032-1-05-80-00-00-01-0](#) [1031-2-05-80-00-00-01-0](#) [1030-3-05-80-00-00-01-0](#) [1213-0-05-01-00-00-01-0](#) [1095-0-05-01-00-00-01-0](#) [1032-1-05-01-00-00-01-0](#) [1031-2-05-01-00-00-01-0](#) [1030-3-05-01-00-00-01-0](#) [1302-0-05-80-00-00-01-0](#) [1216-0-05-80-00-00-01-0](#) [0318-3-05-21-00-00-01-0](#) [1030-3-05-15-00-00-01-0](#) [1030-3-05-21-00-00-01-0](#) [1031-2-05-15-00-00-01-0](#) [1031-2-05-21-00-00-01-0](#) [1032-1-05-15-00-00-01-0](#) [1032-1-05-21-00-00-01-0](#) [1095-0-05-15-00-00-01-0](#) [1095-0-05-21-00-00-01-0](#) [1214-0-05-15-00-00-01-0](#) [1216-0-05-15-00-00-01-0](#) [1216-0-05-21-00-00-01-0](#)