



2304/2305




2304-X-00-XX-00-00-07-0
Swage mount in .076 hole



2305-X-00-XX-00-00-07-0
Swage mount in .076 hole

- X -	Board Thickness	Length V
1	.031	.051
2	.062	.082
3	.094	.113
4	.125	.145


2503



2503-X-00-XX-00-00-07-0
Swage mount in .082 hole

- X -	Board Thickness	Length V	Depth D
1	.031	.078	.068
2	.062	.109	.098
3	.094	.141	
4	.125	.172	


2704




2704-X-00-XX-00-00-07-0
Swage mount in .082 hole

- X -	Board Thickness	Length V
1	.031	.075
2	.062	.105
3	.094	.135
4	.125	.165


2306/2307/2311



2306-X-00-XX-00-00-07-0
Swage mount in .076 hole



2307-X-00-XX-00-00-07-0
Swage mount in .076 hole



2311-X-00-XX-00-00-07-0
Swage mount in .076 hole

- X -	Board Thickness	Length V
1	.031	.051
2	.062	.082
3	.094	.113
4	.125	.145

SPECIFICATIONS

PIN MATERIAL:
Brass Alloy 360, 1/2 Hard
Swage pins are annealed

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - 07 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 44 300μ" SILVER OVER COPPER (RoHS)
- ◇ 50 300μ" ELECTRO-SOLDER (RoHS) (60/40 SnPb)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[2311-4-00-01-00-00-07-0](#) [2311-4-00-50-00-00-07-0](#) [2307-4-00-01-00-00-07-0](#) [2307-4-00-50-00-00-07-0](#) [2306-4-00-01-00-00-07-0](#) [2306-4-00-50-00-00-07-0](#) [2307-4-00-80-00-00-07-0](#) [2306-4-00-44-00-00-07-0](#) [2307-4-00-44-00-00-07-0](#) [2311-4-00-44-00-00-07-0](#)