



1802/3802/4030/8866



Basic Part Number	Length A
1802-0	3,18
3802-0	4,19
8866-0	19,69
4030-0	20,70

XXXX-0-15-XX-XX-XX-04-0
Press-fit in 1,45 mounting hole


1803/1805/1808/3805



Basic Part Number	Length A
1808-0	2,54
1803-0	3,68
1805-0	5,41
3805-0	9,98

XXXX-0-15-XX-43-XX-04-0
Press-fit in 1,45 mounting hole


1804/1806



Basic Part Number	Length A
1804-0	2,03
1806-0	2,92


180X-0-15-XX-43-XX-04-0
Press-fit in 1,45 mounting hole

1807




1807-0-15-XX-43-XX-04-0
Press-fit in 1,45 mounting hole

8830




8830-0-15-XX-22-XX-10-0
Solder mount in 1,45 min. mounting hole

8363




8363-0-15-XX-35-XX-10-0
Solder mount in 1,45 min. mounting hole

4622



4622-0-15-XX-30-XX-10-0
Hex press-fit in 1,35 plated thru hole

6252



6252-0-15-XX-32-XX-10-0
Hex press-fit in 1,45 plated thru hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: $\pm 0,13$
DIAMETERS: $\pm 0,05$
ANGLES: $\pm 2^\circ$

ORDER CODE: XXXX - X - 15 - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08 μ m TIN/LEAD OVER NICKEL
- 80 5,08 μ m TIN OVER NICKEL (RoHS)
- 15 0,25 μ m GOLD OVER NICKEL (RoHS)



SPECIFY CONTACT FINISH:

- 02 2,54 μ m TIN/LEAD OVER NICKEL
- 84 2,54 μ m TIN OVER NICKEL (RoHS)
- 27 0,76 μ m GOLD OVER NICKEL (RoHS)

SELECT CONTACT

#22, #30, #32 or #43 CONTACT (DATA ON PAGES 218, 219 & 220)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[1802-0-15-01-32-02-04-0](#) [1802-0-15-80-30-84-04-0](#) [1802-0-15-15-30-27-04-0](#) [1802-0-15-01-32-27-04-0](#) [1802-0-15-80-32-84-04-0](#) [1802-0-15-80-30-27-04-0](#) [1802-0-15-01-30-27-04-0](#) [1802-0-15-01-30-02-04-0](#) [1802-0-15-15-32-27-04-0](#) [1802-0-15-80-32-27-04-0](#)