


PIN RECEPTACLES

FOR 0,81 - 1,17 DIAMETER PINS

0344

0344-X-19-XX-34-XX-10-0

Swage mount in 1,70 hole




Basic Part Number	Board Thickness	Length V	Depth D
0344-1	0,78	1,57	1,02
0344-2	1,57	2,39	1,57
0344-3	2,39	3,18	1,57
0344-4	3,18	3,96	1,57

0349

0349-X-31-XX-34-XX-10-0

Swage mount in 3,28 hole




Basic Part Number	Board Thickness	Length V
0349-2	1,57	2,39
0349-3	2,39	3,18
0349-4	3,18	3,96

0323

0323-X-15-XX-34-XX-10-0


Swage mount in 2,39 hole



0324

0324-X-15-XX-34-XX-10-0

Swage mount in 2,39 hole




Basic Part Number	Board Thickness	Length V
032X-1	0,79	1,57
032X-2	1,57	2,39
032X-3	2,39	3,18
032X-4	3,18	3,96
032X-5	4,78	5,56

0348

0348-0-33-XX-34-XX-10-0


Wire crimp termination. Accepts wire sizes 20 AWG Max. / 24 AWG Min.



0405

0405-0-15-XX-34-XX-04-0


Press-fit in 2,13 mounting hole



0336

0336-0-15-XX-34-XX-04-0


Press-fit in 2,26 mounting hole



0322

0322-0-15-XX-34-XX-10-0


Solder mount in 2,26 min. mounting hole



0325

0325-0-15-XX-34-XX-10-0

Press-fit in 2,29 mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$

RoHS-2
2011/65/EU

ORDER CODE: XXXX - X - XX - XX - 34 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◆ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◆ 15 0,25µm GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◆ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◆ 27 0,76µm GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#34 CONTACT (DATA ON PAGE 258)

(For alternate contact choices, see group E on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0349-4-31-80-34-80-10-0](#) [0349-4-31-80-34-27-10-0](#) [0349-3-31-80-34-27-10-0](#) [0349-2-31-80-34-80-10-0](#) [0349-2-31-80-34-27-10-0](#) [0344-4-19-80-34-27-10-0](#) [0344-3-19-80-34-27-10-0](#) [0344-2-19-80-34-27-10-0](#) [0344-1-19-80-34-27-10-0](#) [0336-0-15-80-34-27-04-0](#) [0325-0-15-80-34-27-10-0](#) [0324-5-15-80-34-80-10-0](#) [0324-4-15-80-34-27-10-0](#) [0324-3-15-80-34-80-10-0](#) [0324-3-15-80-34-27-10-0](#) [0324-2-15-80-34-80-10-0](#) [0324-1-15-80-34-80-10-0](#) [0324-1-15-80-34-27-10-0](#) [0323-5-15-80-34-27-10-0](#) [0323-4-15-80-34-80-10-0](#) [0323-4-15-80-34-27-10-0](#) [0323-2-15-80-34-80-10-0](#) [0323-2-15-80-34-27-10-0](#) [0323-1-15-80-34-80-10-0](#) [0323-1-15-80-34-27-10-0](#) [0349-4-31-01-34-01-10-0](#) [0349-4-31-01-34-27-10-0](#) [0349-3-31-01-34-01-10-0](#) [0349-3-31-01-34-27-10-0](#) [0349-2-31-01-34-27-10-0](#) [0344-4-19-01-34-01-10-0](#) [0344-4-19-01-34-27-10-0](#) [0344-3-19-01-34-01-10-0](#) [0344-3-19-01-34-27-10-0](#) [0344-1-19-01-34-27-10-0](#) [0325-0-15-01-34-01-10-0](#) [0324-5-15-01-34-01-10-0](#) [0324-5-15-01-34-27-10-0](#) [0324-4-15-01-34-01-10-0](#) [0324-4-15-01-34-27-10-0](#) [0324-3-15-01-34-01-10-0](#) [0324-3-15-01-34-27-10-0](#) [0324-2-15-01-34-27-10-0](#) [0323-5-15-01-34-01-10-0](#) [0323-5-15-01-34-27-10-0](#) [0323-4-15-01-34-01-10-0](#) [0323-4-15-01-34-27-10-0](#) [0323-3-15-01-34-01-10-0](#) [0323-3-15-01-34-27-10-0](#) [0323-2-15-01-34-01-10-0](#) [0323-2-15-01-34-27-10-0](#) [0323-4-15-15-34-27-10-0](#) [0323-5-15-15-34-27-10-0](#) [0324-2-15-15-34-27-10-0](#) [0324-3-15-15-34-27-10-0](#) [0324-4-15-15-34-27-10-0](#) [0344-1-19-15-34-27-10-0](#) [0344-3-19-15-34-27-10-0](#) [0349-2-31-15-34-27-10-0](#) [0349-3-31-15-34-27-10-0](#)