


**■ Features :**

- AC input 180~264VAC
- Protections: Short circuit / Overload / Over voltage/Over temperature
- Leakage current<1mA
- Forced air cooling by built-in DC fan
- Low profile:30mm
- Withstand 300vac surge input for 5 second
- LED indicator for power on
- Conformal coating
- Low cost,high reliability
- 100% full load burn-in test
- 2 years warranty

User's Manual


**■ GTIN CODE**


MW Search: <https://www.meanwell.com/serviceGTIN.aspx>

**SPECIFICATION**

| MODEL               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | NEL-400-2.8                                                                                                             | NEL-400-4.2 | NEL-400-5  |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------|-------------|------------|
| OUTPUT              | DC VOLTAGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   | 2.8V                                                                                                                    | 4.2V        | 5V         |
|                     | RATED CURRENT                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | 80A                                                                                                                     | 80A         | 80A        |
|                     | CURRENT RANGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | 0 ~ 80A                                                                                                                 | 0 ~ 80A     | 0 ~ 80A    |
|                     | RATED POWER                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | 224W                                                                                                                    | 336W        | 400W       |
|                     | RIPPLE & NOISE (max.) <small>Note.2</small>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | 150mVp-p                                                                                                                | 150mVp-p    | 150mVp-p   |
|                     | VOLTAGE ADJ. RANGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | 2.5 ~ 3V                                                                                                                | 3.6 ~ 4.4V  | 4.5 ~ 5.5V |
|                     | VOLTAGE TOLERANCE <small>Note.3</small>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | +3%,-4.5%                                                                                                               | +3%,-4.5%   | ±3.0%      |
|                     | LINE REGULATION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | ±0.5%                                                                                                                   | ±0.5%       | ±0.5%      |
|                     | LOAD REGULATION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | ±2.5%                                                                                                                   | ±2.5%       | ±2.0%      |
|                     | SETUP, RISE TIME                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | 2500ms, 50ms/230VAC                                                                                                     |             |            |
| HOLD UP TIME (Typ.) | 20ms/230VAC                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |                                                                                                                         |             |            |
| INPUT               | VOLTAGE RANGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | 180 ~ 264VAC    254 ~ 370VDC                                                                                            |             |            |
|                     | FREQUENCY RANGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | 47 ~ 63Hz                                                                                                               |             |            |
|                     | EFFICIENCY (Typ.)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | 79%                                                                                                                     | 83%         | 84%        |
|                     | AC CURRENT (Typ.)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | 3A/230VAC                                                                                                               | 4A/230VAC   | 5A/230VAC  |
|                     | INRUSH CURRENT (Typ.)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        | 100A/230VAC                                                                                                             |             |            |
|                     | LEAKAGE CURRENT                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | <1mA / 240VAC                                                                                                           |             |            |
| PROTECTION          | OVER LOAD                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | 105 ~ 140% rated output power<br>Protection type : Hiccup mode, recovers automatically after fault condition is removed |             |            |
|                     | OVER VOLTAGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 | 3.22 ~ 3.78V                                                                                                            | 4.6 ~ 5.4V  | 5.6 ~ 7V   |
|                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | Protection type :Hiccup mode, recovers automatically after fault condition is removed                                   |             |            |
|                     | OVER TEMPERATURE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | Shut down O/P voltage, recovers automatically after temperature goes down                                               |             |            |
| ENVIRONMENT         | WORKING TEMP.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                | -20 ~ +60℃ (Refer to output load derating curve)                                                                        |             |            |
|                     | WORKING HUMIDITY                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | 20 ~ 90% RH non-condensing                                                                                              |             |            |
|                     | STORAGE TEMP., HUMIDITY                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | -20 ~ +85℃, 10 ~ 95% RH                                                                                                 |             |            |
|                     | TEMP. COEFFICIENT                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | ±0.03%/℃ (0 ~ 50℃ )                                                                                                     |             |            |
|                     | VIBRATION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | 10 ~ 500Hz, 3G 10min./1cycle, 60min. each along X, Y, Z axes                                                            |             |            |
| SAFETY & EMC        | SAFETY STANDARDS                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | UL 62368-1,EAC TP TC 004 approved                                                                                       |             |            |
|                     | WITHSTAND VOLTAGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | I/P-O/P:3KVAC    I/P-FG:2KVAC    O/P-FG:0.5KVAC                                                                         |             |            |
|                     | ISOLATION RESISTANCE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | I/P-O/P, I/P-FG, O/P-FG:100M Ohms/500VDC / 25℃ / 70% RH                                                                 |             |            |
|                     | EMC EMISSION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 | Compliance to EAC TP TC 020                                                                                             |             |            |
|                     | EMC IMMUNITY                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 | Compliance to EAC TP TC 020                                                                                             |             |            |
| OTHERS              | MTBF                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | 1708.9K hrs min.    Telcordia SR-332 (Bellcore) ; 220.9Khrs min.    MIL-HDBK-217F (25℃)                                 |             |            |
|                     | DIMENSION                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | 215*115*30mm (L*W*H)                                                                                                    |             |            |
|                     | PACKING                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | 0.85Kg;15pcs/13.8Kg/0.67CUFT                                                                                            |             |            |
| NOTE                | 1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25℃ of ambient temperature.<br>2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor.<br>3. Tolerance : includes set up tolerance, line regulation and load regulation.<br>※ Product Liability Disclaimer : For detailed information, please refer to <a href="https://www.meanwell.com/serviceDisclaimer.aspx">https://www.meanwell.com/serviceDisclaimer.aspx</a> |                                                                                                                         |             |            |

## Mechanical Specification


Case No. 207D Unit:mm Tolerance:±1




Terminal Pin No. assignment :

| Pin No. | Assignment | Pin No. | Assignment   |
|---------|------------|---------|--------------|
| 1       | AC/L       | 4~6     | DC OUTPUT -V |
| 2       | AC/N       | 7~9     | DC OUTPUT +V |
| 3       | FG $\perp$ |         |              |


## Block Diagram



## Derating Curve



## Static Characteristics



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[MEAN WELL:](#)

[NEL-400-4.2](#) [NEL-400-5](#) [NEL-400-2.8](#)