


MALE PCB PINS

PRINTED CIRCUIT PINS

0504/0505

050X-0-00-XX-00-00-03-0

Press-fit in 1,45 mounting hole



Basic Part Number

0504-0
0505-0


Pin Material

Phosphor Bronze 544
Brass 360

5510/5511

551X-0-00-XX-00-00-03-0

Press-fit in 1,45 mounting hole



Basic Part Number

5510-0
5511-0


Standoff Height S

8,41
15,39

4259

4259-X-00-XX-00-00-03-0

Press-fit in 1,45 mounting hole



Basic Part Number

4259-1
4259-2
4259-3
4259-4


Standoff Height S

5,33
8,51
14,86
21,21

3516

3516-0-00-XX-00-00-03-0


Press-fit in 1,45 mounting hole



8859

8859-0-00-XX-00-00-03-0


Press-fit in 1,42 mounting hole



6585

6585-0-00-XX-00-00-03-0


Press-fit in 1,45 mounting hole
Pin material is Phosphor Bronze 544 (B2)



3404

3404-0-00-XX-00-00-03-0


Press-fit in 1,45 mounting hole



3169

3169-0-00-15-00-00-03-0

V-Groove Header Pin
Also available on Kapton Tape



SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Except where noted)

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - 03 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08 μ m TIN/LEAD OVER NICKEL
- ◆ 80 5,08 μ m TIN OVER NICKEL (RoHS)
- ◆ 15 0,25 μ m GOLD OVER NICKEL (RoHS)
- ◆ 21 0,51 μ m GOLD OVER NICKEL (RoHS)
- ◆ 34 1,27 μ m GOLD OVER NICKEL (RoHS)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[3516-0-00-01-00-00-03-0](#) [3516-0-00-80-00-00-03-0](#) [0504-0-00-21-00-00-03-0](#) [0505-0-00-15-00-00-03-0](#) [0505-0-00-34-00-00-03-0](#) [4259-1-00-15-00-00-03-0](#) [4259-1-00-21-00-00-03-0](#) [4259-2-00-15-00-00-03-0](#) [4259-3-00-34-00-00-03-0](#) [4259-4-00-15-00-00-03-0](#) [4259-4-00-21-00-00-03-0](#) [4259-4-00-34-00-00-03-0](#) [5510-0-00-15-00-00-03-0](#) [5510-0-00-21-00-00-03-0](#) [3404-0-00-34-00-00-03-0](#) [3404-0-00-80-00-00-03-0](#) [3404-0-00-21-00-00-03-0](#)