


MALE PCB PINS

PRINTED CIRCUIT PINS

1752/6458

XXXX-0-00-XX-00-00-03-0

Press-fit in 1,45 mounting hole




Basic Part Number	Length K
1752-0	0,51
6458-0	0,89

3413/8404

X4XX-0-00-XX-00-00-03-0

Press-fit in 1,45 mounting hole




Basic Part Number	Length S
3413-0	3,0
8404-0	3,33

9075

9075-0-00-XX-00-00-03-0


Press-fit in 0,86 mounting hole



9218

9218-0-00-XX-00-00-03-0


Press-fit in 1,45 mounting hole



5607

5607-0-01-XX-00-00-03-0


Compliant press-fit in 1,02 ± 0,08 plated hole. For 1,52 → 2,54 thick board



2617

2617-0-01-XX-00-00-03-0


Compliant press-fit in 1,02 ± 0,08 plated hole. For 1,52 → 2,54 thick board



8995

8995-0-01-XX-00-00-03-0


Compliant press-fit in 1,02 ± 0,08 plated hole. For 1,52 → 2,54 thick board



1933

1933-0-00-XX-00-00-03-0


Press-fit in 0,86 mounting hole



1935

1935-0-00-XX-00-00-03-0

Press-fit in 0,86 mounting hole



SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Except where noted)

Dimensions: Millimeters

Tolerances On: Lengths: ± 0,13
Diameters: ± 0,051
Angles: ± 2°

RoHS-2
2011/65/EU

ORDER CODE: XXXX - X - 0X - XX - 00 - 00 - 03 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◆ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◆ 15 0,25µm GOLD OVER NICKEL (RoHS)
- ◆ 21 0,51µm GOLD OVER NICKEL (RoHS)
- ◆ 34 1,27µm GOLD OVER NICKEL (RoHS)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[9218-0-00-01-00-00-03-0](#) [9218-0-00-80-00-00-03-0](#) [3413-0-00-80-00-00-03-0](#) [1752-0-00-80-00-00-03-0](#) [1752-0-00-21-00-00-03-0](#) [1752-0-00-34-00-00-03-0](#) [3413-0-00-21-00-00-03-0](#) [3413-0-00-34-00-00-03-0](#) [9075-0-00-21-00-00-03-0](#) [9075-0-00-34-00-00-03-0](#) [9218-0-00-34-00-00-03-0](#)