

INTERCONNECTS

SERIES 451 • 2,54 GRID INTERCONNECT HEADERS • DOUBLE ROW STRIPS




FIG. 1




FIG. 2





FIG. 3

- Series 451 interconnect header strips come in three lengths with 0,46 dia. pluggable solder tails at one end and 0,64 dia. pins at the other. Please see series:
451...003 uses pin #5503
451...004 uses pin #5504
451...005 uses pin #5505
- 0,46 pluggable solder tails are available at both ends. Please see series:
451...009 uses pin #5509
451...010 uses pin #5510
451...011 uses pin #5511
See pages 212 and 214 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 451...003	0,46 / 0,64 Dia. Solder Tails
	451-10-2	-00-003000
	Specify number of pins	04-64
FIG. 2	Series 451...009	0,46 / 0,46 Dia. Solder Tails
	451-10-2	-00-009000
	Specify number of pins	04-64
FIG. 3	Series 451...004	0,46 / 0,64 Dia. Solder Tails
	451-10-2	-00-004000
	Specify number of pins	04-64
FIG. 3	Series 451...010	0,46 / 0,46 Dia. Solder Tails
	451-10-2	-00-010000
	Specify number of pins	04-64
FIG. 3	Series 451...005	0,46 / 0,64 Dia. Solder Tails
	451-10-2	-00-005000
	Specify number of pins	04-64
FIG. 3	Series 451...011	0,46 / 0,46 Dia. Solder Tails
	451-10-2	-00-011000
	Specify number of pins	04-64
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264		
SPECIFY PLATING CODE XX=		
Pin Plating 		
10 		
0,25µm Au		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[451-10-264-00-011000](#) [451-10-264-00-010000](#) [451-10-264-00-009000](#) [451-10-264-00-005000](#) [451-10-264-00-004000](#) [451-10-264-00-003000](#) [451-10-204-00-004000](#) [451-10-216-00-010000](#) [451-10-212-00-004000](#) [451-10-222-00-005000](#) [451-10-224-00-005000](#) [451-10-204-00-005000](#) [451-10-226-00-009000](#) [451-10-232-00-005000](#) [451-10-252-00-010000](#)