


MALE PCB PINS

SOLDER TERMINALS SLOTTED

2303

2303-X-01-XX-00-00-07-0


Swage mount in 1,63 hole



2323

2323-X-01-XX-00-00-07-0


Swage mount in 1,63 hole



2322

2322-X-01-XX-00-00-07-0

Swage mount in 1,63 hole




Basic Part Number	Board Thickness	Length V
23XX-1	0,79	1,35
23XX-2	1,57	2,13
23XX-3	2,39	2,92
23XX-4	3,18	3,73

2320

2320-X-01-XX-00-00-07-0

Swage mount in 1,63 hole




Basic Part Number	Board Thickness	Length V
2320-1	0,79	1,35
2320-2	1,57	2,13
2320-3	2,39	2,92

2328

2328-X-01-XX-00-00-07-0

Swage mount in 1,63 hole




Basic Part Number	Board Thickness	Length V
2328-1	0,79	1,57
2328-2	1,57	2,39
2328-3	2,39	3,18
2328-4	3,18	3,96

2520

2520-X-01-XX-00-00-07-0


Swage mount in 1,63 hole



2517

2517-X-01-XX-00-00-07-0

Swage mount in 1,63 hole



Basic Part Number	Board Thickness	Length V
25XX-1	0,79	1,57
25XX-2	1,57	2,39
25XX-3	2,39	3,18
25XX-4	3,18	3,96

SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Swage pins are annealed)

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 01 - XX - 00 - 00 - 07 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 44 7,62μm SILVER OVER COPPER (RoHS)
- 50 7,62μm ELECTRO-SOLDER (60/40 SnPb)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[2520-4-01-01-00-00-07-0](#) [2520-4-01-50-00-00-07-0](#) [2520-3-01-01-00-00-07-0](#) [2520-3-01-50-00-00-07-0](#) [2520-2-01-01-00-00-07-0](#) [2520-2-01-50-00-00-07-0](#) [2520-1-01-01-00-00-07-0](#) [2517-4-01-01-00-00-07-0](#) [2517-4-01-50-00-00-07-0](#) [2517-3-01-01-00-00-07-0](#) [2517-3-01-50-00-00-07-0](#) [2517-2-01-01-00-00-07-0](#) [2517-2-01-50-00-00-07-0](#) [2517-1-01-01-00-00-07-0](#) [2517-1-01-50-00-00-07-0](#) [2328-4-01-01-00-00-07-0](#) [2328-4-01-50-00-00-07-0](#) [2328-3-01-01-00-00-07-0](#) [2328-3-01-50-00-00-07-0](#) [2328-2-01-01-00-00-07-0](#) [2328-2-01-50-00-00-07-0](#) [2328-1-01-01-00-00-07-0](#) [2328-1-01-50-00-00-07-0](#) [2323-4-01-01-00-00-07-0](#) [2323-4-01-50-00-00-07-0](#) [2323-3-01-01-00-00-07-0](#) [2323-3-01-50-00-00-07-0](#) [2323-2-01-50-00-00-07-0](#) [2323-1-01-01-00-00-07-0](#) [2323-1-01-50-00-00-07-0](#) [2322-4-01-01-00-00-07-0](#) [2322-4-01-50-00-00-07-0](#) [2322-3-01-50-00-00-07-0](#) [2322-2-01-01-00-00-07-0](#) [2322-2-01-50-00-00-07-0](#) [2322-1-01-01-00-00-07-0](#) [2322-1-01-50-00-00-07-0](#) [2320-3-01-01-00-00-07-0](#) [2320-3-01-50-00-00-07-0](#) [2320-2-01-01-00-00-07-0](#) [2320-2-01-50-00-00-07-0](#) [2320-1-01-01-00-00-07-0](#) [2320-1-01-50-00-00-07-0](#) [2303-4-01-01-00-00-07-0](#) [2303-4-01-50-00-00-07-0](#) [2303-3-01-01-00-00-07-0](#) [2303-3-01-50-00-00-07-0](#) [2303-2-01-50-00-00-07-0](#) [2303-1-01-01-00-00-07-0](#) [2520-4-01-80-00-00-07-0](#) [2520-3-01-80-00-00-07-0](#) [2520-2-01-80-00-00-07-0](#) [2520-1-01-80-00-00-07-0](#) [2517-3-01-80-00-00-07-0](#) [2328-4-01-80-00-00-07-0](#) [2328-3-01-80-00-00-07-0](#) [2328-1-01-80-00-00-07-0](#) [2323-4-01-80-00-00-07-0](#) [2323-3-01-80-00-00-07-0](#) [2323-1-01-80-00-00-07-0](#) [2322-2-01-80-00-00-07-0](#) [2322-1-01-80-00-00-07-0](#) [2320-3-01-80-00-00-07-0](#) [2320-1-01-80-00-00-07-0](#) [2303-4-01-80-00-00-07-0](#) [2303-3-01-80-00-00-07-0](#) [2303-1-01-80-00-00-07-0](#) [2303-1-01-44-00-00-07-0](#) [2303-4-01-44-00-00-07-0](#) [2320-1-01-44-00-00-07-0](#) [2320-2-01-44-00-00-07-0](#) [2320-3-01-44-00-00-07-0](#) [2322-1-01-44-00-00-07-0](#) [2322-2-01-44-00-00-07-0](#) [2322-4-01-44-00-00-07-0](#) [2323-1-01-44-00-00-07-0](#) [2323-2-01-44-00-00-07-0](#) [2323-4-01-44-00-00-07-0](#) [2328-1-01-44-00-00-07-0](#) [2328-2-01-44-00-00-07-0](#) [2328-3-01-44-00-00-07-0](#) [2328-4-01-44-00-00-07-0](#) [2517-1-01-44-00-00-07-0](#) [2517-2-01-44-00-00-07-0](#) [2517-3-01-44-00-00-07-0](#) [2517-4-01-44-00-00-07-0](#) [2520-1-01-44-00-00-07-0](#) [2520-2-01-44-00-00-07-0](#) [2520-3-01-44-00-00-07-0](#) [2520-4-01-44-00-00-07-0](#)