


MALE PCB PINS

SOLDER TERMINALS PIN TYPE

2319

2319-X-00-XX-00-00-07-0

Swage mount in 1,93 hole




Basic Part Number	Board Thickness	Length V
2319-1	0,79	1,30
2319-2	1,57	2,08
2319-3	2,39	2,87

2313

2313-X-00-XX-00-00-07-0

Swage mount in 1,93 hole




Basic Part Number	Board Thickness	Length V
2313-1	0,79	1,30
2313-2	1,57	2,13
2313-3	2,39	2,87
2313-4	3,18	3,68

2321

2321-X-00-XX-00-00-07-0

Swage mount in 1,93 hole




Basic Part Number	Board Thickness	Length V
2321-1	0,79	1,30
2321-2	1,57	2,08
2321-3	2,39	2,87
2321-4	3,18	3,68

2706

2706-X-00-XX-00-00-07-0

Swage mount in 3,05 hole




Basic Part Number	Board Thickness	Length V
2706-1	0,79	1,60
2706-2	1,57	2,36
2706-3	2,39	3,18
2706-4	3,18	3,96

2530

2530-X-00-XX-00-00-07-0

Swage mount in 2,39 hole




Basic Part Number	Board Thickness	Length V
2530-2	1,57	2,39
2530-3	2,39	3,18
2530-4	3,18	3,96

3156

3156-X-00-XX-00-00-08-0

Swage mount in 1,93 hole



Basic Part Number	Board Thickness	Length V
3156-1	0,79	1,30
3156-2	1,57	2,08
3156-3	2,39	2,87
3156-4	3,18	3,68

SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Swage pins are annealed)

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - XX - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 44 7,62μm SILVER OVER COPPER (RoHS)
- 50 7,62μm ELECTRO-SOLDER
(60/40 SnPb)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[3156-4-00-01-00-00-08-0](#) [3156-3-00-01-00-00-08-0](#) [3156-1-00-01-00-00-08-0](#) [2706-4-00-01-00-00-07-0](#) [2706-4-00-50-00-00-07-0](#) [2706-3-00-50-00-00-07-0](#) [2706-1-00-01-00-00-07-0](#) [2706-1-00-50-00-00-07-0](#) [2530-4-00-50-00-00-07-0](#) [2530-3-00-01-00-00-07-0](#) [2530-2-00-50-00-00-07-0](#) [2321-4-00-50-00-00-07-0](#) [2321-3-00-50-00-00-07-0](#) [2321-2-00-01-00-00-07-0](#) [2319-3-00-01-00-00-07-0](#) [2319-3-00-50-00-00-07-0](#) [2319-2-00-01-00-00-07-0](#) [2319-2-00-50-00-00-07-0](#) [2313-4-00-01-00-00-07-0](#) [2313-4-00-50-00-00-07-0](#) [2313-3-00-01-00-00-07-0](#) [2313-3-00-50-00-00-07-0](#) [2313-2-00-01-00-00-07-0](#) [2313-2-00-50-00-00-07-0](#) [2313-1-00-50-00-00-07-0](#) [3156-4-00-80-00-00-08-0](#) [3156-3-00-80-00-00-08-0](#) [3156-1-00-80-00-00-08-0](#) [2706-3-00-80-00-00-07-0](#) [2706-1-00-80-00-00-07-0](#) [2530-3-00-80-00-00-07-0](#) [2321-4-00-80-00-00-07-0](#) [2321-3-00-80-00-00-07-0](#) [2321-2-00-80-00-00-07-0](#) [2321-1-00-80-00-00-07-0](#) [2319-3-00-80-00-00-07-0](#) [2319-1-00-80-00-00-07-0](#) [2313-2-00-80-00-00-07-0](#) [2313-1-00-80-00-00-07-0](#) [2313-1-00-44-00-00-07-0](#) [2313-2-00-44-00-00-07-0](#) [2313-3-00-44-00-00-07-0](#) [2313-4-00-44-00-00-07-0](#) [2319-1-00-44-00-00-07-0](#) [2319-2-00-44-00-00-07-0](#) [2319-3-00-44-00-00-07-0](#) [2321-1-00-44-00-00-07-0](#) [2321-3-00-44-00-00-07-0](#) [2321-4-00-44-00-00-07-0](#) [2530-4-00-44-00-00-07-0](#) [2706-1-00-44-00-00-07-0](#) [2706-3-00-44-00-00-07-0](#) [2321-3-00-01-00-00-07-0](#)