


MALE PCB PINS

SOLDER TERMINALS SLOTTED

2315

2315-X-01-XX-00-00-07-0

Swage mount in 1,70 hole




Basic Part Number	Board Thickness	Length V	Depth D
2315-1	0,79	1,14	1,02
2315-2	1,57	2,39	1,57
2315-3	2,39	3,18	1,57
2315-4	3,18	3,96	1,57

2302

2302-X-01-XX-00-00-07-0

Swage mount in 1,70 hole




Basic Part Number	Board Thickness	Length V
2302-1	0,79	1,35
2302-2	1,57	2,13
2302-3	2,39	2,92
2302-4	3,18	3,73

2352

2352-X-01-XX-00-00-07-0

Swage mount in 1,70 hole




Basic Part Number	Board Thickness	Length V
2352-1	0,79	1,14
2352-2	1,57	2,39
2352-3	2,39	3,18
2352-4	3,18	3,96

2362

2362-X-01-XX-00-00-07-0

Swage mount in 1,70 hole




Basic Part Number	Board Thickness	Length V
2362-5	0,41	0,94
2362-1	0,79	1,35
2362-2	1,57	2,13
2362-3	2,39	2,92
2362-4	3,18	3,73

2507

2507-X-01-XX-00-00-07-0


Swage mount in 1,70 hole



2526

2526-X-01-XX-00-00-07-0

Swage mount in 1,63 hole



Basic Part Number	Board Thickness	Length V
25XX-1	0,79	1,35
25XX-2	1,57	2,13
25XX-3	2,39	2,92
25XX-4	3,18	3,73

SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Swage pins are annealed)

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 01 - XX - 00 - 00 - 07 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 44 7,62μm SILVER OVER COPPER (RoHS)
- 50 7,62μm ELECTRO-SOLDER (60/40 SnPb)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[2526-4-01-01-00-00-07-0](#) [2526-4-01-50-00-00-07-0](#) [2526-3-01-01-00-00-07-0](#) [2526-3-01-50-00-00-07-0](#) [2526-2-01-50-00-00-07-0](#) [2526-1-01-01-00-00-07-0](#) [2526-1-01-50-00-00-07-0](#) [2507-4-01-01-00-00-07-0](#) [2507-4-01-50-00-00-07-0](#) [2507-3-01-01-00-00-07-0](#) [2507-3-01-50-00-00-07-0](#) [2507-2-01-50-00-00-07-0](#) [2507-1-01-50-00-00-07-0](#) [2362-5-01-01-00-00-07-0](#) [2362-5-01-50-00-00-07-0](#) [2362-4-01-01-00-00-07-0](#) [2362-4-01-50-00-00-07-0](#) [2362-3-01-01-00-00-07-0](#) [2362-3-01-50-00-00-07-0](#) [2362-2-01-01-00-00-07-0](#) [2362-2-01-50-00-00-07-0](#) [2362-1-01-01-00-00-07-0](#) [2362-1-01-50-00-00-07-0](#) [2352-4-01-01-00-00-07-0](#) [2352-4-01-50-00-00-07-0](#) [2352-2-01-50-00-00-07-0](#) [2352-1-01-01-00-00-07-0](#) [2352-1-01-50-00-00-07-0](#) [2315-4-01-01-00-00-07-0](#) [2315-4-01-50-00-00-07-0](#) [2315-3-01-01-00-00-07-0](#) [2315-3-01-50-00-00-07-0](#) [2315-1-01-50-00-00-07-0](#) [2302-4-01-01-00-00-07-0](#) [2302-4-01-50-00-00-07-0](#) [2302-3-01-01-00-00-07-0](#) [2302-3-01-50-00-00-07-0](#) [2302-1-01-01-00-00-07-0](#) [2302-1-01-50-00-00-07-0](#) [2315-2-01-50-00-00-07-0](#) [2526-4-01-80-00-00-07-0](#) [2526-2-01-80-00-00-07-0](#) [2526-1-01-80-00-00-07-0](#) [2507-4-01-80-00-00-07-0](#) [2507-3-01-80-00-00-07-0](#) [2362-5-01-80-00-00-07-0](#) [2362-4-01-80-00-00-07-0](#) [2362-3-01-80-00-00-07-0](#) [2362-2-01-80-00-00-07-0](#) [2362-1-01-80-00-00-07-0](#) [2352-4-01-80-00-00-07-0](#) [2352-3-01-80-00-00-07-0](#) [2352-2-01-80-00-00-07-0](#) [2352-1-01-80-00-00-07-0](#) [2315-4-01-80-00-00-07-0](#) [2315-3-01-80-00-00-07-0](#) [2302-4-01-80-00-00-07-0](#) [2302-3-01-80-00-00-07-0](#) [2302-1-01-80-00-00-07-0](#) [2302-2-01-44-00-00-07-0](#) [2302-3-01-44-00-00-07-0](#) [2302-4-01-44-00-00-07-0](#) [2315-1-01-44-00-00-07-0](#) [2315-3-01-44-00-00-07-0](#) [2315-4-01-44-00-00-07-0](#) [2352-3-01-44-00-00-07-0](#) [2352-4-01-44-00-00-07-0](#) [2362-3-01-44-00-00-07-0](#) [2362-4-01-44-00-00-07-0](#) [2362-5-01-44-00-00-07-0](#) [2507-1-01-44-00-00-07-0](#) [2507-3-01-44-00-00-07-0](#) [2507-4-01-44-00-00-07-0](#) [2526-2-01-44-00-00-07-0](#) [2526-4-01-44-00-00-07-0](#) [2352-3-01-01-00-00-07-0](#)