


PIN RECEPTACLES

FOR .025" - .037" DIAMETER PINS AND .025" SQUARE PINS

1305

1305-0-15-XX-47-XX-04-0


Press-fit in .061 mounting hole



1306

1306-0-15-XX-47-XX-04-0


Press-fit in .061 mounting hole



7305

7305-0-15-XX-47-XX-10-0


Solder mount in .060 min. mounting hole
Also available on 8mm wide carrier tape:
6,000 parts per 13" reel
Order as: 7305-0-57-XX-47-XX-10-0



0400

0400-0-15-XX-47-XX-04-0


Press-fit in .067 mounting hole



0335

0335-0-15-XX-47-XX-04-0


Hex press-fit in .064 plated through-hole



4614

4614-0-31-XX-47-XX-04-0


Compliant press-fit in .040 ± .003 plated hole. For .060" → .100" thick board



4615

4615-0-31-XX-47-XX-04-0


Compliant press-fit in .040 ± .003 plated hole. For .090" → .130" thick board



7614

7614-0-31-XX-47-XX-04-0


Compliant press-fit in .040 ± .003 plated hole. For .060" → .100" thick board



8401

8401-0-15-XX-47-XX-04-0


Hex press-fit in .063 plated through-hole



2400

2400-0-15-XX-47-XX-04-0


Press-fit in .066 mounting hole



6857

6857-0-15-XX-47-XX-10-0


Press-fit in .062 mounting hole



9393

9393-0-15-XX-47-XX-10-0

Press-fit in .067 mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: ±.005

Diameters: ±.002

Angles: ± 2°



ORDER CODE: XXXX - X - XX - XX - 47 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

01 200 μ" TIN/LEAD OVER NICKEL

◆ 80 200 μ" TIN OVER NICKEL (RoHS)

◆ 15 10 μ" GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

01 200 μ" TIN/LEAD OVER NICKEL

◆ 80 200 μ" TIN OVER NICKEL (RoHS)

◆ 27 30 μ" GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#47 CONTACT (DATA ON PAGE 256)

(For alternate contact choices, see group D on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[4615-0-31-01-47-01-04-0](#) [4614-0-31-01-47-27-04-0](#) [2400-0-15-01-47-01-04-0](#) [2400-0-15-01-47-27-04-0](#) [0400-0-15-80-47-80-04-0](#) [0335-0-15-80-47-80-04-0](#) [0335-0-15-80-47-27-04-0](#) [1306-0-15-01-47-27-04-0](#) [1305-0-15-01-47-27-04-0](#) [0400-0-15-01-47-27-04-0](#) [0335-0-15-01-47-27-04-0](#) [9393-0-15-80-47-80-10-0](#) [6857-0-15-80-47-80-10-0](#) [2400-0-15-80-47-80-04-0](#) [1306-0-15-80-47-27-04-0](#) [1305-0-15-80-47-27-04-0](#) [0335-0-15-15-47-27-04-0](#) [6857-0-15-15-47-27-10-0](#) [0400-0-15-01-47-01-04-0](#)