


- Features :
 - 3000VDC I/O isolation
 - Internal SMD technology
 - Built-in EMI filter
 - Protection: Short circuit
 - Cooling by free air convection
 - Non-conductive plastic case
 - Single in line package
 - 100% full load burn-in test
 - Low cost / High reliability
 - 2 years warranty



SPECIFICATION

ORDER NO.	SPU02L-05	SPU02M-05	SPU02N-05	SPU02L-12	SPU02M-12	SPU02N-12	SPU02L-15	SPU02M-15	SPU02N-15
OUTPUT	DC OUTPUT VOLTAGE	5V			12V			15V	
	CURRENT RANGE	80 ~ 400mA			33 ~ 167mA			27 ~ 133mA	
	EFFICIENCY (Typ.)	77%	79%	77%	80%	81%	80%	81%	82%
	RATED POWER	2W							
	RIPPLE & NOISE (max.) Note.2	100mVp-p							
	LINE REGULATION Note.3	±1.2% for 1% input variation							
	LOAD REGULATION Note.4	±8.0%							
	VOLTAGE ACCURACY	±2.0%							
	SWITCHING FREQUENCY	100KHz min.							
INPUT	VOLTAGE RANGE	4.5 ~ 5.5V	10.8 ~ 13.2V	21.6 ~ 26.4V	4.5 ~ 5.5V	10.8 ~ 13.2V	21.6 ~ 26.4V	4.5 ~ 5.5V	10.8 ~ 13.2V
	NORMAL VOLTAGE	5V	12V	24V	5V	12V	24V	5V	12V
	INPUT CURRENT	Full load	520mA	214mA	107mA	520mA	214mA	107mA	520mA
		No load	60mA	20mA	15mA	60mA	20mA	15mA	60mA
	FILTER	Capacitor type							
PROTECTION	PROTECTION	Fuse recommended							
	OVERLOAD	Momentary							
		Protection type : Broken							
	SHORT CIRCUIT	Momentary							
ENVIRONMENT		Protection type : Broken							
	WORKING TEMP.	-40 ~ +71°C (Refer to "Derating Curve")							
	WORKING HUMIDITY	20% ~ 90% RH non-condensing							
	STORAGE TEMP., HUMIDITY	-40 ~ +105°C, 10 ~ 95% RH							
	TEMP. COEFFICIENT	±0.03% / °C (0 ~ 50°C)							
SAFETY & EMC	VIBRATION	10 ~ 500Hz, 2G 10min./1 cycle, period for 60min. each along X, Y, Z axes							
	WITHSTAND VOLTAGE	I/P-O/P: 3KVDC							
	ISOLATION RESISTANCE	I/P-O/P: 100M Ohms / 500VDC / 25°C / 70% RH							
	ISOLATION CAPACITANCE	80pF max.							
	EMC EMISSION	Compliance to EN55032 Class B, FCC part 15 Class B							
OTHERS	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8, light industry level, criteria A							
	MTBF	700khrs min. MIL-HDBK-217F(25°C)							
	DIMENSION	19.6*7.1*10.2mm or 0.77**0.28**0.40" inch (L*W*H)							
	WEIGHT	2.3g							


Mechanical Specification



Pin Configuration

Pin No.	Output
1	+Vin
2	-Vin
5	-Vout
7	+Vout

Derating Curve



NOTE

1. All parameters are specified at normal input, rated load, 25°C 70% RH ambient.
2. Ripple & noise are measured at 20MHz by using a 12" twisted pair terminated with a 0.1uF & 47uF capacitor.
3. Line regulation is measured from low line to high line at rated load.
4. Load regulation is measured from 20% to 100% rated load.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

MEAN WELL:

[SPU02M-12](#) [SPU02L-15](#) [SPU02N-05](#) [SPU02M-05](#) [SPU02N-12](#) [SPU02M-15](#) [SPU02L-05](#) [SPU02L-12](#) [SPU02N-15](#)