


PIN RECEPTACLES

FOR 0,81 - 1,17 DIAMETER PINS

8838

8838-0-15-XX-34-XX-10-0


Solder mount in 2,18 min. mounting hole



3100

3100-0-15-XX-34-XX-10-0


Solder mount in 1,88 min. mounting hole



8853

8853-0-15-XX-34-XX-10-0


Press-fit in 1,8 mounting hole



6800

6800-0-15-XX-34-XX-04-0


Solder mount in 2,03 min. mounting hole



0739

0739-0-15-XX-34-XX-10-0


Hex press-fit in 1,98 plated through-hole




8206

8206-0-15-XX-34-XX-40-0

Surface mount, board edge




P.C.B. Layout



0720

0720-0-33-XX-34-XX-10-0


Wire crimp termination. Accepts wire sizes 20 AWG Max. / 24 AWG Min.



5084

5084-0-18-XX-34-XX-10-0

Press-fit in 2,06 mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$

Diameters: $\pm 0,051$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 15 - XX - 34 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

01 5,08µm TIN/LEAD OVER NICKEL

◆ 80 5,08µm TIN OVER NICKEL (RoHS)

◆ 15 0,25µm GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

01 5,08µm TIN/LEAD OVER NICKEL

◆ 80 5,08µm TIN OVER NICKEL (RoHS)

◆ 27 0,76µm GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#34 CONTACT (DATA ON PAGE 258)

(For alternate contact choices, see group E on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[3100-0-15-01-34-01-10-0](#) [8853-0-15-80-34-27-10-0](#) [3100-0-15-80-34-27-10-0](#)