


# PIN RECEPTACLES

**FOR 0,56 - 0,86 DIAMETER PINS AND 0,64 SQUARE PINS**

## 9808

**9808-0-15-XX-16-XX-04-0**


Press-fit in 1,70 mounting hole



## 9101

**9101-0-15-XX-16-XX-10-0**


Press-fit in 1,70 mounting hole



## 5650

**5650-0-19-XX-16-XX-10-0**


Press-fit in 1,70 mounting hole



## 8679

**8679-0-15-XX-16-XX-10-0**


Solder mount in 1,80 min. mounting hole



## 6021

**6021-0-15-XX-16-XX-10-0**


Solder mount in 1,57 min. mounting hole  
Also available on 24mm wide carrier tape:  
1,500 parts per 330mm reel  
Order as: 6021-0-57-XX-16-XX-10-0



## 1873

**1873-0-15-XX-16-XX-04-0**


Press-fit in 1,68 mounting hole



## 8827

**8827-0-15-XX-16-XX-04-0**


Press-fit in 1,55 mounting hole



## 5070

**5070-0-18-XX-16-XX-10-0**

Press-fit in 1,55 mounting hole



### SPECIFICATIONS:

**Shell Material:** Brass Alloy 360, 1/2 Hard

**Contact Material:** Beryllium Copper Alloy 172, HT

**Dimensions:** Millimeters

**Tolerances On:** Lengths:  $\pm 0,13$

Diameters:  $\pm 0,051$

Angles:  $\pm 2^\circ$



**ORDER CODE:** XXXX - X - XX - XX - 16 - XX - 10 - 0

**BASIC PART #**

**SPECIFY SHELL FINISH:**

**01** 5,08 $\mu$ m TIN/LEAD OVER NICKEL

◆ **80** 5,08 $\mu$ m TIN OVER NICKEL (RoHS)

◆ **15** 0,25 $\mu$ m GOLD OVER NICKEL (RoHS)

**SPECIFY CONTACT FINISH:**

**01** 5,08 $\mu$ m TIN/LEAD OVER NICKEL

◆ **80** 5,08 $\mu$ m TIN OVER NICKEL (RoHS)

◆ **27** 0,76 $\mu$ m GOLD OVER NICKEL (RoHS)

**SELECT CONTACT:**

**#16** CONTACT (DATA ON PAGE 256)

(For alternate contact choices, see group D on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[1873-0-15-80-16-80-04-0](#) [1873-0-15-80-16-27-04-0](#) [9808-0-15-15-16-27-04-0](#) [8827-0-15-80-16-80-04-0](#) [8827-0-15-80-16-27-04-0](#)