



Preliminary Datasheet

Dimensions mm[inch]




tolerances acc. to DIN ISO 2768-m
Toleranzen gem. DIN ISO 2768-m




Isometric

Scale 2:1
Maßstab 2:1




Test circuit



Layout

Top view
Draufsicht



Marking

according to EN60062/factory code
gem. EN60062/Fertigungsstätte

MEDER 522-03-i
KIWA 18ATEX0017 U 0344
Ex II (1) G Ex ia Ga IIC YMP

Elect. Coupler Characteristic	Conditions	Min	Typ	Max	Unit
Turn-on Time 1 Ton	If=10mA, Uce=5V, RL=100 Ohm		5,5		µS
Turn-Off Time 1 Toff	If=10mA, Uce=5V, RL=100 Ohm		4,2		µS
Current Transfer Ratio Ic/If CTR	If=10 mA	0,5	0,8		
Cut-Off Frequency 1 Fco	If=10mA, Uce=5V, RL=100 Ohm		50		kHz
Insulation Resistance Input/Output	RH 45%	1.000			GOhm
Insulation Voltage Input/Output Uio		4.000			VDC
Coupling capacitance Cc			0,4		pF
Creeping Distance		12			mm
Air Path Input/Output		12			mm
Insulation Distance Emitter-Detecto		2			mm

Maximum Ratings Emitter	Conditions	Min	Typ	Max	Unit
Forward Voltage Uf	If=10 mA			1,5	V
DC Forward Current If				75	mA
Reverse Voltage Ur	Ir=100 microA			5	V
Surge Forward current Ifs	t<=10 ms			500	mA
Power Dissipation Ptot				170	mW

Maximum Ratings Detector	Conditions	Min	Typ	Max	Unit
Collector-Emitter Voltage Vce				32	VDC
Emitter-Collector Voltage Vec				5	VDC
Collector Dark Current Iceo	Uce=20V, R=1MOhm, If=0mA			0,2	µA
Collector-Emitter Saturation Voltag	If=10 mA, Ic=1 mA		0,3		VDC
Collector Peak Current Icm				100	mA
Collector Current Ic				50	mA
Power Dissipation Ptot				100	mW



Europe: +49 / 7731 8399 0

| Email: info@standexmeder.com

USA: +1 / 508 295 0771

| Email: salesusa@standexmeder.com

Asia: +852 / 2955 1682

| Email: salesasia@standexmeder.com

Item No.:

5252203000

Item:

522-03-i

Preliminary Datasheet

Special Product Data	Conditions	Min	Typ	Max	Unit
Connection pins			cu-alloy tinned		
Case colour			blue		
Housing material			Plastic		
Reach / RoHS conformity			yes		
Sealing compound			Polyurethan		
Approval			KIWA 18ATEX0017 U		
Approval			IECEX KIWA 18.0009U		

Environmental data	Conditions	Min	Typ	Max	Unit
Ambient Temperature Ta		-40		85	°C
Storage temperature		-40		100	°C
Soldering temperature	wave soldering max. 5 sec.			260	°C
Shock	1/2 sine, duration 11ms, in 3 axis			50	g
Vibration	from 10 - 2000 Hz			20	g
Washability			fully sealed		

Modifications in the sense of technical progress are reserved

Designed at: 06.04.09 Designed by: KSCHIELENSKI Approval at: 10.01.14 Approval by: KOLBRICH

Last Change at: 14.12.18 Last Change by: SSCHNECKENBURGER Approval at: Approval by:

Version: 12

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Standex Electronics:](#)

[522-03-I](#)