


MALE PCB PINS

PRINTED CIRCUIT PINS • NAIL HEAD TYPE

4209

4209-0-00-XX-00-00-33-0


Solder mount in 0,56 mounting hole



5063

5063-0-00-XX-00-00-33-0


Solder mount in 0,61 mounting hole



4965

4965-0-00-XX-00-00-33-0


Solder mount in 0,61 mounting hole



6547

6547-0-00-XX-00-00-33-0


Solder mount in 0,61 mounting hole



4071

4071-0-00-XX-00-00-33-0


Solder mount in 0,61 mounting hole



8808

8808-0-00-XX-00-00-33-0


Solder mount in 0,61 mounting hole



4964

4964-0-00-XX-00-00-33-0


Solder mount in 0,61 mounting hole



9185

9185-0-00-XX-00-00-33-0


Solder mount in 0,67 mounting hole



8257

8257-0-00-XX-00-00-33-0


Solder mount in 0,66 mounting hole



5035

5035-0-00-XX-00-00-33-0


Solder mount in 0,74 mounting hole



5240

5240-0-00-XX-00-00-33-0


Solder mount in 0,74 mounting hole



2650

2650-0-00-XX-00-00-33-0

Solder mount in 0,74 mounting hole



SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Except where noted)

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$

RoHS-2
2011/65/EU

ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - XX - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08 μ m TIN/LEAD OVER NICKEL
- ◆ 80 5,08 μ m TIN OVER NICKEL (RoHS)
- ◆ 15 0,25 μ m GOLD OVER NICKEL (RoHS)
- ◆ 21 0,51 μ m GOLD OVER NICKEL (RoHS)
- ◆ 34 1,27 μ m GOLD OVER NICKEL (RoHS)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

9185-0-00-80-00-00-33-0