



- Series 518 Interstitial PGA sockets are available with and without tabs for clip-on heatsinks.
- Mill-Max #43, “Ultra-Lite” contact standard, see page 209 for details.
- Hi-Temp PCT polyester insulator material suitable for all forms of soldering.
- A pry-bar tool is available for extraction (part # 828-01-010).




SOLDER TAIL SOCKET PIN (Without Heatsink Tabs)



Pin Type	
02	For L = .125"
03	For L = .145"
08	For L = .100"

PIN 08 IS USED EXCLUSIVELY IN CERTAIN PATTERNS. SEE CHART "A".

SOLDER TAIL SOCKET PIN (With Heatsink Tabs)



Pin Type	
04	For L = .080"
06	For L = .115"

PIN 08 IS USED EXCLUSIVELY IN CERTAIN PATTERNS. SEE CHART "A".

Ordering Information

Interstitial configurations are a .100" grid pattern overlapped with a second, staggered .100" grid pattern thus doubling the package density of the socket.

1. Locate interstitial footprint pattern from pages 107 to 111, the middle 8 digits of the part number will be located under the pattern.
2. Specify 2-digit plating code from chart at bottom of page.
3. Determine the last 2 digits of part number from the pin type at left.
For sockets with heatsink tabs, see chart “**A**” below for pin options.

Series Plating Code Window Pin Type

5 1 8 - - - - - - 0 - -

No. of pins Grid size Pattern #

Determined from footprint pattern pages 107 to 111

CHART A

FOOTPRINT PATTERN	HEATSINK MFG.	PIN TYPE
296-19-126	THERMALLOY	04, 06
296-19-127	THERMALLOY	04, 06
320-19-126	THERMALLOY	04, 06
296-19-128	WAKEFIELD	04, 06
296-69-129008	SEE NOTE**	08 ONLY
320-69-129008	SEE NOTE**	08 ONLY
387-01-016508	SEE NOTE**	08 ONLY


NOTE**



Designed to work with:
THERMALLOY
WAKEFIELD
AAVID
IERC
heatsinks & clips.

EXAMPLE OF COMPLETE PART NUMBER:

518-93-325-18-105003

This is a 325 pin interstitial (11x11 grid) insulator with a 1.00" square window and fitted with standard solder tail receptacles. Pin sleeve is tin plated, inner contacts are Mill-Max #43 and are plated 30u" gold.



SPECIFY PLATING CODE XX=	13		93	
Sleeve (Pin) 	10μ" Au		200μ" Sn/Pb	
Contact (Clip) 	30μ" Au		30μ" Au	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

518-93-296-69-129002