



7132



7132-0-15-XX-30-XX-04-0

Square press-fit for 0,81 ±0,05
plated thru hole


8445



8445-0-15-XX-30-XX-04-0

Square press-fit for 0,99 ±0,05
plated thru hole


1038



1038-0-15-XX-30-XX-04-0

Press-fit in 1,5 mounting hole


1261



1261-0-15-XX-30-XX-04-0

Press-fit in 1,45 mounting hole

0153




0153-X-15-XX-30-XX-04-0

Press-fit in 1,45 mounting hole

Basic Part Number	Height A
0153-1	5,99
0153-2	8,0
0153-3	10,21
0153-4	11,99
0153-5	15,09
0153-6	17,75

1602/1610




16XX-0-15-XX-30-XX-04-0

Press-fit in 1,45 mounting hole

Basic Part Number	Height A
1602-0	11,2
1610-0	16,31

0903/0904




090X-0-15-XX-30-XX-04-0

Press-fit in 1,45 mounting hole

Basic Part Number	Height A
0903-0	21,36
0904-0	28,98


0144



0144-0-15-XX-30-XX-04-0

Press-fit in 1,45 mounting hole

8252



8252-0-15-XX-30-XX-10-0

Press-fit in 1,45 plated thru hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

PART MANUFACTURED IN
INCHES, METRIC FOR REF ONLY

TOLERANCES ON:
LENGTHS: ± 0,13
DIAMETERS: ± 0,05
ANGLES: ± 2°

ORDER CODE: **XXXX - X - 15 - XX - 30 - XX - XX - 0**

BASIC PART #

SPECIFY SHELL FINISH:
01 5,08µm TIN/LEAD OVER NICKEL

80 5,08µm TIN OVER NICKEL

15 0,25µm GOLD OVER NICKEL

SPECIFY CONTACT FINISH:

02 2,54µm TIN/LEAD OVER NICKEL

84 2,54µm TIN OVER NICKEL

27 0,76µm GOLD OVER NICKEL

CONTACT

#30 CONTACT (DATA ON PAGE 208)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0144-0-15-15-30-27-04-0](#) [0144-0-15-01-30-27-04-0](#) [0144-0-15-01-30-02-04-0](#) [0144-0-15-80-30-84-04-0](#) [0144-0-15-80-30-27-04-0](#)