



Utilizing the latest Field Stop and Trench Gate technologies, these IGBT's have ultra low  $V_{CE(ON)}$  and are ideal for low frequency applications that require absolute minimum conduction loss. Easy paralleling is a result of very tight parameter distribution and a slightly positive  $V_{CE(ON)}$  temperature coefficient. Low gate charge simplifies gate drive design and minimizes losses.

- 600V Field Stop
- Trench Gate: Low  $V_{CE(on)}$
- Easy Paralleling
- 6 $\mu$ s Short Circuit Capability
- 175°C Rated



**Applications: Welding, Inductive Heating, Solar Inverters, SMPS, Motor drives, UPS**

### MAXIMUM RATINGS

All Ratings:  $T_C = 25^\circ\text{C}$  unless otherwise specified.

| Symbol         | Parameter   | APT30GN60BD_SDQ2(G) | UNIT             |
|----------------|---|---------------------|------------------|
| $V_{CES}$      | Collector-Emitter Voltage                                   | 600                 | Volts            |
| $V_{GE}$       | Gate-Emitter Voltage  | $\pm 30$            |                  |
| $I_{C1}$       | Continuous Collector Current @ $T_C = 25^\circ\text{C}$     | 63                  | Amps             |
| $I_{C2}$       | Continuous Collector Current @ $T_C = 110^\circ\text{C}$    | 37                  |                  |
| $I_{CM}$       | Pulsed Collector Current <sup>①</sup>                       | 90                  |                  |
| SSOA           | Switching Safe Operating Area @ $T_J = 150^\circ\text{C}$   | 90A @ 600V          |                  |
| $P_D$          | Total Power Dissipation                                     | 203                 | Watts            |
| $T_J, T_{STG}$ | Operating and Storage Junction Temperature Range            | -55 to 175          | $^\circ\text{C}$ |
| $T_L$          | Max. Lead Temp. for Soldering: 0.063" from Case for 10 Sec. | 300                 |                  |

### STATIC ELECTRICAL CHARACTERISTICS

| Symbol        | Characteristic / Test Conditions   | MIN | TYP | MAX | Units    |
|---------------|--|-----|-----|-----|----------|
| $V_{(BR)CES}$ | Collector-Emitter Breakdown Voltage ( $V_{GE} = 0V, I_C = 2mA$ )                                 | 600 |     |     | Volts    |
| $V_{GE(TH)}$  | Gate Threshold Voltage ( $V_{CE} = V_{GE}, I_C = 430\mu A, T_J = 25^\circ\text{C}$ )             | 5.0 | 5.8 | 6.5 |          |
| $V_{CE(ON)}$  | Collector-Emitter On Voltage ( $V_{GE} = 15V, I_C = 30A, T_J = 25^\circ\text{C}$ )               | 1.1 | 1.5 | 1.9 |          |
|               | Collector-Emitter On Voltage ( $V_{GE} = 15V, I_C = 30A, T_J = 125^\circ\text{C}$ )              |     | 1.7 |     |          |
| $I_{CES}$     | Collector Cut-off Current ( $V_{CE} = 600V, V_{GE} = 0V, T_J = 25^\circ\text{C}$ ) <sup>②</sup>  |     |     | 50  | $\mu A$  |
|               | Collector Cut-off Current ( $V_{CE} = 600V, V_{GE} = 0V, T_J = 125^\circ\text{C}$ ) <sup>②</sup> |     |     | TBD |          |
| $I_{GES}$     | Gate-Emitter Leakage Current ( $V_{GE} = \pm 20V$ )  |     |     | 300 | nA       |
| $R_{G(int)}$  | Intergrated Gate Resistor  |     | N/A |     | $\Omega$ |



**CAUTION:** These Devices are Sensitive to Electrostatic Discharge. Proper Handling Procedures Should Be Followed.

## DYNAMIC CHARACTERISTICS

APT30GN60BD\_SDQ2(G)

| Symbol       | Characteristic                                     | Test Conditions  | MIN | TYP  | MAX | UNIT          |
|--------------|--|--|-----|------|-----|---------------|
| $C_{ies}$    | Input Capacitance                                  | <b>Capacitance</b><br>$V_{GE} = 0V, V_{CE} = 25V$<br>$f = 1 \text{ MHz}$   |     | 1750 |     | pF            |
| $C_{oes}$    | Output Capacitance                                 |  |     | 70   |     |               |
| $C_{res}$    | Reverse Transfer Capacitance                       |  |     | 50   |     |               |
| $V_{GEP}$    | Gate-to-Emitter Plateau Voltage                    | Gate Charge<br>$V_{GE} = 15V$<br>$V_{CE} = 300V$<br>$I_C = 30A$  |     | 9.0  |     | V             |
| $Q_g$        | Total Gate Charge <sup>③</sup>                     |  |     | 165  |     |               |
| $Q_{ge}$     | Gate-Emitter Charge                                |  |     | 10   |     |               |
| $Q_{gc}$     | Gate-Collector ("Miller") Charge                   |  |     | 90   |     |               |
| SSOA         | Switching Safe Operating Area                      | $T_J = 150^\circ\text{C}, R_G = 4.3\Omega^{\text{⑦}}, V_{GE} = 15V, L = 100\mu\text{H}, V_{CE} = 600V$   | 90  |      |     | A             |
| SCSOA        | Short Circuit Safe Operating Area                  | $V_{CC} = 360V, V_{GE} = 15V, T_J = 150^\circ\text{C}, R_G = 4.3\Omega^{\text{⑦}}$   | 6   |      |     | $\mu\text{s}$ |
| $t_{d(on)}$  | Turn-on Delay Time                                 | <b>Inductive Switching (25°C)</b><br>$V_{CC} = 400V$<br>$V_{GE} = 15V$<br>$I_C = 30A$<br>$R_G = 4.3\Omega^{\text{⑦}}$<br>$T_J = +25^\circ\text{C}$   |     | 12   |     | ns            |
| $t_r$        | Current Rise Time                                  |  |     | 14   |     |               |
| $t_{d(off)}$ | Turn-off Delay Time                                |  |     | 155  |     |               |
| $t_f$        | Current Fall Time                                  |  |     | 55   |     |               |
| $E_{on1}$    | Turn-on Switching Energy <sup>④</sup>              |  |     | 525  |     |               |
| $E_{on2}$    | Turn-on Switching Energy (With Diode) <sup>⑤</sup> |  |     | 565  |     |               |
| $E_{off}$    | Turn-off Switching Energy <sup>⑥</sup>             |  |     | 700  |     |               |
| $t_{d(on)}$  | Turn-on Delay Time                                 | <b>Inductive Switching (125°C)</b><br>$V_{CC} = 400V$<br>$V_{GE} = 15V$<br>$I_C = 30A$<br>$R_G = 4.3\Omega^{\text{⑦}}$<br>$T_J = +125^\circ\text{C}$ |     | 12   |     | ns            |
| $t_r$        | Current Rise Time                                  |  |     | 14   |     |               |
| $t_{d(off)}$ | Turn-off Delay Time                                |  |     | 180  |     |               |
| $t_f$        | Current Fall Time                                  |  |     | 75   |     |               |
| $E_{on1}$    | Turn-on Switching Energy <sup>④</sup>              |  |     | 555  |     |               |
| $E_{on2}$    | Turn-on Switching Energy (With Diode) <sup>⑤</sup> |  |     | 950  |     |               |
| $E_{off}$    | Turn-off Switching Energy <sup>⑥</sup>             |  |     | 895  |     |               |

## THERMAL AND MECHANICAL CHARACTERISTICS

| Symbol          | Characteristic                    | MIN | TYP | MAX | UNIT |
|-----------------|-----------------------------------|-----|-----|-----|------|
| $R_{\theta JC}$ | Junction to Case ( <b>IGBT</b> )  |     |     | .74 | °C/W |
| $R_{\theta JC}$ | Junction to Case ( <b>DIODE</b> ) |     |     | .67 |      |
| $W_T$           | Package Weight                    |     | 5.9 |     | gm   |

① Repetitive Rating: Pulse width limited by maximum junction temperature.

② For Combi devices,  $I_{ces}$  includes both IGBT and diode leakages

③ See MIL-STD-750 Method 3471.

④  $E_{on1}$  is the clamped inductive turn-on energy of the IGBT only, without the effect of a commutating diode reverse recovery current adding to the IGBT turn-on loss. Tested in inductive switching test circuit shown in figure 21, but with a Silicon Carbide diode.

⑤  $E_{on2}$  is the clamped inductive turn-on energy that includes a commutating diode reverse recovery current in the IGBT turn-on switching loss. (See Figures 21, 22.)


⑥  $E_{off}$  is the clamped inductive turn-off energy measured in accordance with JEDEC standard JESD24-1. (See Figures 21, 23.)

⑦  $R_G$  is external gate resistance, not including  $R_{Gint}$  nor gate driver impedance. (MIC4452)


Microsemi reserves the right to change, without notice, the specifications and information contained herein.

**TYPICAL PERFORMANCE CURVES**


**APT30GN60BD\_SDQ2(G)**




**FIGURE 1, Output Characteristics ( $T_J = 25^\circ\text{C}$ )**




**FIGURE 2, Output Characteristics ( $T_J = 125^\circ\text{C}$ )**




**FIGURE 3, Transfer Characteristics**




**FIGURE 4, Gate Charge**




**FIGURE 5, On State Voltage vs Gate-to-Emitter Voltage**



**FIGURE 6, On State Voltage vs Junction Temperature**



**FIGURE 7, Breakdown Voltage vs. Junction Temperature**



**FIGURE 8, DC Collector Current vs Case Temperature**




FIGURE 9, Turn-On Delay Time vs Collector Current




FIGURE 10, Turn-Off Delay Time vs Collector Current




FIGURE 11, Current Rise Time vs Collector Current




FIGURE 12, Current Fall Time vs Collector Current




FIGURE 13, Turn-On Energy Loss vs Collector Current




FIGURE 14, Turn Off Energy Loss vs Collector Current




FIGURE 15, Switching Energy Losses vs. Gate Resistance




FIGURE 16, Switching Energy Losses vs Junction Temperature

### TYPICAL PERFORMANCE CURVES




Figure 17, Capacitance vs Collector-To-Emitter Voltage

### APT30GN60BD\_SDQ2(G)




Figure 18, Minimum Switching Safe Operating Area




Figure 19, Maximum Effective Transient Thermal Impedance, Junction-To-Case vs Pulse Duration




Figure 20, Operating Frequency vs Collector Current




Figure 21, Inductive Switching Test Circuit




Figure 22, Turn-on Switching Waveforms and Definitions




Figure 23, Turn-off Switching Waveforms and Definitions

# ULTRAFAST SOFT RECOVERY ANTI-PARALLEL DIODE

## MAXIMUM RATINGS

All Ratings:  $T_C = 25^\circ\text{C}$  unless otherwise specified.

| Symbol       | Characteristic / Test Conditions  | APT30GN60BD_SDQ2(G) |     | UNIT |
|--------------|---|---------------------|-----|------|
| $I_{F(AV)}$  | Maximum Average Forward Current ( $T_C = 111^\circ\text{C}$ , Duty Cycle = 0.5) |                     | 40  | Amps |
| $I_{F(RMS)}$ | RMS Forward Current (Square wave, 50% duty)                                     |                     | 63  |      |
| $I_{FSM}$    | Non-Repetitive Forward Surge Current ( $T_J = 45^\circ\text{C}$ , 8.3ms)        |                     | 320 |      |

## STATIC ELECTRICAL CHARACTERISTICS

| Symbol | Characteristic / Test Conditions | MIN   | TYP  | MAX | UNIT  |
|--------|----------------------------------|---|------|-----|-------|
| $V_F$  | Forward Voltage                  | $I_F = 30\text{A}$                          | 1.85 |     | Volts |
|        |                                  | $I_F = 60\text{A}$                          | 2.27 |     |       |
|        |                                  | $I_F = 30\text{A}, T_J = 125^\circ\text{C}$ | 1.5  |     |       |

## DYNAMIC CHARACTERISTICS

| Symbol    | Characteristic                   | Test Conditions   | MIN | TYP | MAX | UNIT |
|-----------|----------------------------------|---|-----|-----|-----|------|
| $t_{rr}$  | Reverse Recovery Time            | $I_F = 1\text{A}, di_F/dt = -100\text{A}/\mu\text{s}, V_R = 30\text{V}, T_J = 25^\circ\text{C}$     | -   | 22  |     | ns   |
| $t_{rr}$  | Reverse Recovery Time            | $I_F = 40\text{A}, di_F/dt = -200\text{A}/\mu\text{s}, V_R = 400\text{V}, T_C = 25^\circ\text{C}$   | -   | 25  |     |      |
| $Q_{rr}$  | Reverse Recovery Charge          |   | -   | 35  |     | nC   |
| $I_{RRM}$ | Maximum Reverse Recovery Current |   | -   | 3   | -   | Amps |
| $t_{rr}$  | Reverse Recovery Time            | $I_F = 40\text{A}, di_F/dt = -200\text{A}/\mu\text{s}, V_R = 400\text{V}, T_C = 125^\circ\text{C}$  | -   | 160 |     | ns   |
| $Q_{rr}$  | Reverse Recovery Charge          |   | -   | 480 |     | nC   |
| $I_{RRM}$ | Maximum Reverse Recovery Current |   | -   | 6   | -   | Amps |
| $t_{rr}$  | Reverse Recovery Time            | $I_F = 40\text{A}, di_F/dt = -1000\text{A}/\mu\text{s}, V_R = 400\text{V}, T_C = 125^\circ\text{C}$ | -   | 85  |     | ns   |
| $Q_{rr}$  | Reverse Recovery Charge          |   | -   | 920 |     | nC   |
| $I_{RRM}$ | Maximum Reverse Recovery Current |   | -   | 20  |     | Amps |




FIGURE 24. MAXIMUM EFFECTIVE TRANSIENT THERMAL IMPEDANCE, JUNCTION-TO-CASE vs. PULSE DURATION




Figure 25. Forward Current vs. Forward Voltage




Figure 26. Reverse Recovery Time vs. Current Rate of Change




Figure 27. Reverse Recovery Charge vs. Current Rate of Change




Figure 28. Reverse Recovery Current vs. Current Rate of Change




Figure 29. Dynamic Parameters vs. Junction Temperature




Figure 30. Maximum Average Forward Current vs. Case Temperature




Figure 31. Junction Capacitance vs. Reverse Voltage



# TYPICAL PERFORMANCE CURVES

APT30GN60BD\_SDQ2(G)




Figure 32. Diode Test Circuit

- 1  $I_F$  - Forward Conduction Current
- 2  $di_F/dt$  - Rate of Diode Current Change Through Zero Crossing.
- 3  $I_{RRM}$  - Maximum Reverse Recovery Current.
- 4  $t_{rr}$  - Reverse Recovery Time, measured from zero crossing where diode current goes from positive to negative, to the point at which the straight line through  $I_{RRM}$  and  $0.25 \cdot I_{RRM}$  passes through zero.
- 5  $Q_{rr}$  - Area Under the Curve Defined by  $I_{RRM}$  and  $t_{rr}$ .





Figure 33. Diode Reverse Recovery Waveform and Definitions


## TO-247 Package Outline

e1 SAC: Tin, Silver, Copper



## D<sup>3</sup>PAK Package Outline

e3 SAC: Tin, Silver, Copper



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microchip:](#)

[APT30GN60BDQ2G](#)