

INTERCONNECTS

SERIES 410, 411, 415 • 2,54 GRID SOLDER TAIL • DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4

- Series 41X double row strip sockets are on 2,54 grid
- Various solder tails available: standard length, long for multi-layer boards, very low and ultra low profile. See Mill-Max #1001, #0134, #0501 or #1534 pins. See pages 161, 162 and 165 for details
- Hi-Rel, 4-finger BeCu #12 and #30 contact are rated at 3 amps. See pages 252 and 253 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 410...001		Standard Solder Tail		
	410-XX-2-41-001000 Specify number of pins 04-64				
FIG. 2	Series 411...001		Long Solder Tail		
	411-XX-2-41-001000 Specify number of pins 04-64				
FIG. 3	Series 415...001		Very Low Profile		
	415-XX-2-41-001000 Specify number of pins 04-64				
FIG. 4	Series 415...003		Ultra Low Profile		
	415-XX-2-41-003000 Specify number of pins 04-64				
RoHS - 2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264					
SPECIFY PLATING CODE XX=					
Sleeve (Pin)					
Contact (Clip)					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[415-13-240-41-003000](#) [415-11-234-41-003000](#) [415-11-242-41-003000](#) [415-11-252-41-001000](#) [415-11-260-41-001000](#) [415-13-226-41-003000](#) [415-11-240-41-001000](#) [415-11-256-41-001000](#) [415-11-264-41-001000](#) [415-13-240-41-001000](#) [415-43-262-41-001000](#) [415-91-238-41-001000](#) [415-91-248-41-001000](#) [415-91-264-41-001000](#) [415-93-212-41-001000](#) [415-41-244-41-001000](#) [415-43-232-41-003000](#) [415-43-234-41-001000](#) [415-43-250-41-003000](#) [415-91-250-41-003000](#) [415-91-252-41-001000](#) [415-91-258-41-003000](#) [415-41-246-41-003000](#) [415-41-248-41-001000](#) [415-41-262-41-003000](#) [415-41-242-41-001000](#) [415-43-240-41-001000](#) [415-43-248-41-001000](#) [415-91-240-41-003000](#) [415-91-250-41-001000](#) [415-91-256-41-003000](#) [415-41-264-41-001000](#) [415-43-262-41-003000](#) [415-91-238-41-003000](#) [415-91-254-41-003000](#) [415-91-256-41-001000](#) [415-93-212-41-003000](#) [415-13-248-41-001000](#) [415-41-240-41-001000](#) [415-41-250-41-001000](#) [415-43-248-41-003000](#) [415-43-256-41-003000](#) [415-91-264-41-003000](#) [415-13-258-41-001000](#) [415-41-234-41-001000](#) [415-41-234-41-003000](#) [415-41-260-41-001000](#) [415-43-240-41-003000](#) [415-43-242-41-001000](#) [415-43-250-41-001000](#) [415-43-258-41-001000](#) [415-91-234-41-001000](#) [415-91-234-41-003000](#) [415-91-260-41-001000](#) [415-93-208-41-001000](#) [415-93-208-41-003000](#) [415-41-254-41-003000](#) [415-41-256-41-001000](#) [415-41-264-41-003000](#) [415-43-238-41-001000](#) [415-43-246-41-001000](#) [415-13-258-41-003000](#) [415-41-242-41-003000](#) [415-41-250-41-003000](#) [415-41-252-41-001000](#) [415-41-258-41-003000](#) [415-43-258-41-003000](#) [415-91-242-41-001000](#) [415-91-242-41-003000](#) [415-13-246-41-003000](#) [415-41-240-41-003000](#) [415-41-248-41-003000](#) [415-41-256-41-003000](#) [415-41-258-41-001000](#) [415-43-238-41-003000](#) [415-43-256-41-001000](#) [415-91-240-41-001000](#) [415-91-248-41-003000](#) [415-91-258-41-001000](#) [415-13-262-41-001000](#) [415-41-236-41-001000](#) [415-43-244-41-003000](#) [415-43-252-41-003000](#) [415-91-236-41-001000](#) [415-91-254-41-001000](#) [415-91-262-41-001000](#) [415-41-244-41-003000](#) [415-41-252-41-003000](#) [415-41-254-41-001000](#) [415-41-260-41-003000](#) [415-41-262-41-001000](#) [415-43-242-41-003000](#) [415-43-252-41-001000](#) [415-43-260-41-001000](#) [415-91-252-41-003000](#) [415-91-260-41-003000](#) [415-93-210-41-003000](#) [415-13-248-41-003000](#) [415-13-260-41-001000](#) [415-13-262-41-003000](#)