

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0002066135](#)
Status: **Active**
Overview: Standard .062" Pin and Socket Power Connectors
Description: 1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1854, Male, with Gold (Au) Plated Brass Contact, 24-30 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-1190-003 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	1854
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Standard .062" Pin and Socket Power Connectors
Packaging Alternative	02-06-6130 (Reel)
Product Name	Standard .062"
UPC	800753615830

Physical


Gender	Male
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.419/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.254µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.02-2.29mm
Wire Size AWG	24, 26, 28, 30
Wire Size mm ²	N/A

Material Info

Engineering Number 1854-(550)L

Reference - Drawing Numbers

Packaging Specification [PK-1190-003](#)
 Sales Drawing [SD-1854-X](#)



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[1854 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Insertion Tool	11020001
Manual Extraction Tool	11030002
Hand Crimper - DISTRIBUTION ONLY	638111000
Hand Crimp Tool	638190800

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[02-06-6135](#)