

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010894303

Status:


Active

Overview:

C-Grid Connector Products

Description:

2.54mm Pitch C-Grid Breakaway Header, High Profile, Dual Row, Right-Angle, 30 Circuits, 8.13mm Mating Pin Length, 0.38µm Gold (Au) Selective Plating



Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-70216-001 \(PDF\)](#)

[Application Specification 713080001-AS-000 \(PDF\)](#)

[Packaging Specification PK-70873-0075-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		PCB Headers
Series		70216
Application		Board-to-Board, Signal, Wire-to-Board
Overview		C-Grid Connector Products
Product Name		C-Grid
UPC		800755018837

Physical		
Breakaway		Yes
Circuits (Loaded)		30
Circuits (maximum)		30
Color - Resin		Black
Durability (mating cycles max)		50
Flammability		94V-0
Glow-Wire Capable		No
Lock to Mating Part		None
Material - Metal		Brass, Phosphor Bronze
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Material - Resin		Polyester
Net Weight		2.819/g
Number of Rows		2
Orientation		Right Angle
PC Tail Length		2.79mm
PCB Locator		No
PCB Retention		None
Packaging Type		Tube
Pitch - Mating Interface		2.54mm
Plating min - Mating		3.810µm
Plating min - Termination		3.810µm
Polarized to Mating Part		No
Polarized to PCB		No
Shrouded		No
Stackable		Yes
Temperature Range - Operating		-40° to +105°C
Termination Interface: Style		Through Hole

Electrical		
Current - Maximum per Contact		3.0A
Voltage - Maximum		250V

Solder Process Data

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

70216 Series

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	70216-0287
Reference - Drawing Numbers	
Application Specification	713080001-AS-000
Packaging Specification	PK-70873-0075-001
Product Specification	PS-70216-001
Sales Drawing	SD-70216-001-001

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

10-89-4303