

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0014562153

Status:

Active

Overview:

SL Modular Connectors

Description:

2.54mm Pitch SL Insulation Displacement Connector Assembly, Female, Single Row, Version A, Non-polarized, Wire Size 26 AWG, 0.38µm Gold (Au), 15 Circuits

Documents:

3D Model

Packaging Specification PK-70873-0001-001 (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

Drawing (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Ribbon Cable / Wire Trap Connectors
Series	70400
Comments	Terminals Preloaded
Component Type	Housing
Glow-Wire Capable	No
Overview	SL Modular Connectors
Product Name	SL
UPC	800753760967

Physical	
Circuits (Loaded)	15
Color - Resin	Black
Durability (mating cycles max)	50
Entry Angle	Vertical
Flammability	94V-0
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Number of Rows	1
PCB Retention	None
Packaging Type	Tube
Pitch - Mating Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	1.905µm
Polarized to Mating Part	No
Stackable	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	IDT or Pierce
Wire Insulation Diameter	1.35mm max.
Wire Size AWG	26
Wire/Cable Type	Discrete Wire, Ribbon Cable

Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Material Info	
Engineering Number	70400-0714



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

70400 Series

Mates With

Single Row Headers and Housings, [8624](#) , [70203](#) , [42375](#) , [42377](#)

Use With

[7307](#) Tinned 28AWG, [7767](#) Topcoat 28AWG, [24241](#) Tinned 26AWG, [8996](#) Topcoat 26AWG, [24226](#) Tinned 24AWG, [8997](#) Topcoat 24AWG, [24369](#) High Flex 26AWG, [24389](#) High Flex 24AWG

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
IDT - Semi-automatic	11200949
- Bench-Top Terminator	
IDT Discrete	621000700
Handtool Module	

Reference - Drawing Numbers

Packaging Specification
Sales Drawing

PK-70873-0001-001
SDA-70400-0701-0724

Ribbon Cable Tool 622016600
Kit, Press Not
Included
Hawk Ribbon Cable 623003000
Terminator without
Break-off
Hawk Semi- 623003100
Automatic Discrete
Wire Terminator
Hawk Semi- 623004900
Automatic Discrete
Wire Terminator
for Rebuilt CE
Approved*
Hawk Flat Flex Cable623005200
Terminator with
Break-off
Hawk Ribbon Cable 623005300
Terminator with
Break-off

This document was generated on 07/27/2021
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

14-56-2153