



VTC4 series

Voltage Controlled Temperature Compensated Crystal Oscillator



The VTC4, VCTXCO

Features

- Clipped Sine Wave Output
- Output Frequencies to 27 MHz
- Fundamental Crystal Design
- Optional VCXO Function available
- Gold over nickel contact pads
- Hermetically Sealed Ceramic SMD package
- Product is compliant to RoHS directive  and fully compatible with lead free assembly

Applications

- Wireless Communications
- Base Stations
- Point to point radios
- Broadband Access
- Test Equipment
- Handsets

Description

Vectron's VTC4 Temperature Compensated Crystal Oscillator (TCXO) is a quartz stabilized, clipped sine wave output, temperature compensated oscillator, operating off either a 2.8, 3.0, 3.3 or 5.0 volt supply.

VTC4 Data Sheet

Performance Characteristics

Table 1. Electrical Performance					
Parameter	Symbol	Min	Typical	Maximum	Units
Frequency	f_o	10.000		27.000	MHz
Typical Supply Voltage ¹ <i>Ordering option, see last page</i>		2.8, 3.0, 3.3 or 5.0			V
Supply Current 10.000 MHz to < 15.000 MHz 15.000 MHz to 27.00 MHz	I_{DD}			1.5 2.0	mA
Output Level ²	Vp/p	0.8			V
Output Load			10K 10pf		
Control Voltage Impedance	Z_{Vc}	1			Mohm
Control Voltage to reach pull <i>All options (5.0, 3.3, 3.0 and 2.8V)</i>		0.5		2.5	V
Pull Range <i>Ordering option, see last page</i>	TPR	$\pm 5, \pm 8, \pm 10, \pm 15$			ppm
Temperature Stability <i>Ordering option, see last page.</i>		± 0.5 to ± 5.0			ppm
Initial Accuracy, "No Adjust" option			± 0.5	± 1.0	ppm
Power Supply Stability				± 0.2	ppm
Load Stability				± 0.2	ppm
Aging				± 1.0	ppm/year
Operating temperature <i>Ordering option, see last page</i>		0/55, -10/60, -20/70, -30/80, -40/85			°C
Phase Noise, 12.800MHz 10 Hz offset 100 Hz offset 1 kHz offset 10 kHz offset 100 kHz offset 5MHz offset			-89 -113 -137 -150 -155 -156		dBc/Hz
Start-up time				2	ms

1. A 0.01uF and a 0.1uF capacitor should be located as close to the supply as possible (to ground) is recommended.

2. Output is DC coupled.

VTC4 Data Sheet




Figure 1. Typical Phase Noise Plot




Figure 2. Clipped Sine Wave Output

VCXO Functional Description


VCXO Feature: The VTC4 can be ordered with a VCXO function for applications where it will be used in a PLL, or the output frequency needs fine tune adjustments. This is a high impedance input, 1 Mohm, and can be driven with an op-amp or terminated with adjustable resistors etc. **Pin 1 should not be left floating** on the VCXO optional devices.

“No Adjust” Feature: In applications where the VTC4 will not be used in a PLL, or the output frequency does not fine tune adjustments, the best device to use would be a VTC4-x0xx. By using the “no adjust” option, the circuit is simplified as V_C does not need to be adjusted or set to a predetermined voltage and **pin 1 should be grounded** (pin 1 can be left open but should not be set to a voltage such as the supply).

Outline Diagrams, Pad Layout and Pin Out

Table 2. Pinout		
Pin #	Symbol	Function
1	GND or V_C	Ground for a VTC4-x0xx option or VCXO Control Voltage
2	GND	Electrical and Case Ground
3	f_O	Output Frequency
4	V_{DD}	Supply Voltage

NOTE: Additional pads are used to program and adjust the TCXO during manufacturing and should be left open; do not terminate these to the supply voltage. Some designs do not include these additional pads.



Contact Pads are gold over nickel
Devices will be marked with the frequency


Figure 3, Package drawing

VTC4 Data Sheet

Tape and Reel

Table 3. Tape and Reel Dimensions (mm)

Tape Dimensions						Reel Dimensions							# Per Reel
Product	A	B	C	D	E	F	G	H	I	J	K	L	
VTC4	16	7.5	1.5	4	8	1.5	20.2	13	60	2	16.4	180	1000



Absolute Maximum Ratings

Stresses in excess of the absolute maximum ratings can permanently damage the device. Functional operation is not implied at these or any other conditions in excess of conditions represented in the operational sections of this data sheet. Exposure to absolute maximum ratings for extended periods may adversely affect device reliability.

Table 4. Absolute Maximum Ratings

Parameter	Symbol	Ratings	Unit
Storage Temperature	T _{storage}	-55/125	°C

Table 5. Environmental Compliance

Parameter	Conditions
Mechanical Shock	MIL-STD-883 Method 2002
Mechanical Vibration	MIL-STD-883 Method 2007
Temperature Cycle	MIL-STD-883 Method 1010
Solderability	MIL-STD-883 Method 2003
Gross and Fine Leak	MIL-STD-883 Method 1014
Resistance to Solvents	MIL-STD-883 Method 2015
Moisture Sensitivity Level	1
Contact Pads	Gold over Nickel

Handling Precautions

Although ESD protection circuitry has been designed into the the VTC4, proper precautions should be taken when handling and mounting. VI employs a Human Body Model and a Charged-Device Model (CDM) for ESD susceptibility testing and design protection evaluation. ESD thresholds are dependent on the circuit parameters used to define the model. Although no industry wide standard has been adopted for the CDM, a standard HBM of resistance = 1.5kohms and capacitance = 100pF is widely used and therefore can be used for comparison purposes.

Table 6. ESD Ratings


Model	Minimum	Conditions
Human Body Model	1500	MIL-STD-883 Method 3115
Charged Device Model	1000	JESD 22-C101

Suggested IR profile

Devices are built using lead free epoxy and can also be subjected to standard lead free IR reflow conditions, Table 7 shows max temperatures and lower temperatures can also be used e.g. peak temperature of 220C.

Table 7. Reflow Profile (IPC/JEDEC J-STD-020)

Parameter	Symbol	Value
PreHeat Time	t_s	60 sec Min, 180 sec Max
Ramp Up	R_{UP}	3 °C/sec Max
Time Above 217 °C	t_L	60 sec Min, 150 sec Max
Time To Peak Temperature	t_{AMB-P}	480 sec Max
Time At 260 °C (max)	t_P	10 sec Max
Time At 240 °C (max)	t_{p2}	60 sec Max
Ramp Down	R_{DN}	6 °C/sec Max



Ordering Information

Table 8. Standard Frequency List

10.000	12.504	12.800	13.000	13.568	14.000	14.31818	14.4844
14.7456	15.000	16.000	16.325291	16.367667	16.396	16.800	17.500
18.414	19.200	19.440	19.6608	19.680	19.800	20.000	21.250
23.104	24.000	24.5535	24.576	25.000	25.600	26.000	27.456

VTC4 - **B** **0** **2** **C** - **12M8000000**

Product Family

TCXO, 5x3.2

Voltage Options

A: +5.0 Vdc $\pm 5\%$, Clipped Sine Output
 B: +3.3 Vdc $\pm 5\%$, Clipped Sine Output
 C: +3.0 Vdc $\pm 5\%$, Clipped Sine Output
 D: +2.8 Vdc $\pm 5\%$, Clipped Sine Output

Pulling Range

0: Fixed TCXO, no adjust
 1: ± 5 ppm
 2: ± 8 ppm
 3: ± 10 ppm
 4: ± 15 ppm

Output Frequency (MHz)

Temperature Options

A: 0 to 55 °C
 B: -10 to 60 °C
 C: -20 to 70 °C
 D: -30 to 80 °C
 E: -40 to 85 °C

Stability Options

A: ± 0.5 ppm
 1: ± 1.0 ppm
 B: ± 1.5 ppm
 2: ± 2.0 ppm
 C: ± 2.5 ppm
 3: ± 3.0 ppm
 D: ± 3.5 ppm
 4: ± 4.0 ppm
 5: ± 5.0 ppm

Note: Not all combinations are available:

± 0.5 ppm is available over 0 / 55 °C, and on a case by case basis for -10/60C.
 ± 1.0 ppm to ± 5.0 ppm is available on all temperature range



www.vectron.com

USA: Vectron International • 267 Lowell Road, Suite 102, Hudson, NH 03051
 • Tel: 1-88-VECTRON-1 • Fax: 1-888-FAX-VECTRON

EUROPE: Landstrasse, D-74924, Neckarbischofsheim, Germany
 • Tel: 49 (0) 7268 8010 • Fax: 49 (0) 7268 801281

ASIA: Vectron International • 68 Yin Cheng Road (C), 22nd Floor,
 One LuJiaZui, Pudong, Shanghai 200120, China
 • Tel: 8621 61946886 • Fax: 8621 61946699

Feb 26, 2014

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Microchip:

[VTC4-D12D-19M200000](#) [VTC4-B0CE-19M6800000](#) [VTC4-A1BE-26M0000000](#) [VTC4-A31C-10M0000000](#) [VTC4-B01E-10M0000000](#) [VTC4-B01E-20M0000000](#) [VTC4-B01E-25M0000000](#) [VTC4-B02E-20M0000000](#) [VTC4-B3CD-25M0000000](#) [VTC4-C01E-10M0000000](#) [VTC4-B1AA-10M0000000](#) [VTC4-B21C-26M0000000](#) [VTC4-B31C-10M0000000](#) [VTC4-B31C-20M0000000](#) [VTC4-B32E-25M0000000](#) [VTC4-B3AA-20M0000000](#)