

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015910060

Status:


Active

Overview:

C-Grid Connector Products

Description:

2.54mm Pitch C-Grid Breakaway Header, Surface Mount, Dual Row, Vertical, 6 Circuits, 0.38µm Gold (Au) Selective Plating



Series image - Reference only

Documents:

|                                                          |                                                                  |
|----------------------------------------------------------|------------------------------------------------------------------|
| <a href="#">3D Model</a>                                 | <a href="#">Application Specification 713080001-AS-000 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                            | <a href="#">Packaging Specification 713080001-PK-000 (PDF)</a>   |
| <a href="#">3D Model (PDF)</a>                           | <a href="#">RoHS Certificate of Compliance (PDF)</a>             |
| <a href="#">Product Specification PS-71308-001 (PDF)</a> |                                                                  |

Agency Certification

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

General

|                |                                       |
|----------------|---------------------------------------|
| Product Family | PCB Headers                           |
| Series         | 71308                                 |
| Application    | Board-to-Board, Signal, Wire-to-Board |
| Overview       | C-Grid Connector Products             |
| Product Name   | C-Grid                                |
| UPC            | 800754223010                          |

Physical

|                                |                                |
|--------------------------------|--------------------------------|
| Breakaway                      | Yes                            |
| Circuits (Loaded)              | 6                              |
| Circuits (maximum)             | 6                              |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 50                             |
| Flammability                   | 94V-0                          |
| Glow-Wire Capable              | No                             |
| Lock to Mating Part            | None                           |
| Material - Metal               | Phosphor Bronze                |
| Material - Plating Mating      | Gold                           |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 0.364/g                        |
| Number of Rows                 | 2                              |
| Orientation                    | Vertical                       |
| PCB Locator                    | No                             |
| PCB Retention                  | None                           |
| Packaging Type                 | Bag                            |
| Pitch - Mating Interface       | 2.54mm                         |
| Plating min - Mating           | 0.381µm                        |
| Plating min - Termination      | 2.032µm                        |
| Polarized to Mating Part       | No                             |
| Polarized to PCB               | No                             |
| Shrouded                       | No                             |
| Stackable                      | Yes                            |
| Temperature Range - Operating  | -40° to +105°C                 |
| Termination Interface: Style   | Surface Mount                  |

Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum             | 250V |

Solder Process Data

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

Search Parts in this Series  
71308 Series

|                                                |                  |
|------------------------------------------------|------------------|
| Duration at Max. Process Temperature (seconds) | 005              |
| Lead-freeProcess Capability                    | REFLOW           |
| Max. Cycles at Max. Process Temperature        | 001              |
| Process Temperature max. C                     | 260              |
| <b>Material Info</b>                           |                  |
| Engineering Number                             | 71308-0106N      |
| <b>Reference - Drawing Numbers</b>             |                  |
| Application Specification                      | 713080001-AS-000 |
| Packaging Specification                        | 713080001-PK-000 |
| Product Specification                          | PS-71308-001     |
| Sales Drawing                                  | 713080000-SD-000 |

This document was generated on 09/14/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15-91-0060](#)