

N-CHANNEL J-FET

Equivalent To MIL-PRF-19500/385

DEVICES

2N4856 2N4858 2N4860
2N4857 2N4859 2N4861

LEVELS

MQ = JAN Equivalent
MX = JANTX Equivalent
MV = JANTXV Equivalent

ABSOLUTE MAXIMUM RATINGS ($T_C = +25^\circ\text{C}$ unless otherwise noted)


Parameters / Test Conditions	Symbol	2N4856 2N4857 2N4858	2N4859 2N4860 2N4861	Unit
Gate-Source Voltage	V_{GS}	-40	-30	V
Drain-Source Voltage	V_{DS}	40	30	V
Drain-Gate Voltage	V_{DG}	40	30	V
Gate Current	I_G	50		mA
Power Dissipation $T_A = +25^\circ\text{C}^{(1)}$ $T_C = +25^\circ\text{C}^{(2)}$	P_T	0.36 1.8		W W
Operating Junction & Storage Temperature Range	T_J, T_{stg}	-65 to + 200		$^\circ\text{C}$

(1) Derate linearly 2.06 mW/ $^\circ\text{C}$ for $T_A > +25^\circ\text{C}$.

(2) Derate linearly 10.3 mW/ $^\circ\text{C}$ for $T_C > +25^\circ\text{C}$.

ELECTRICAL CHARACTERISTICS ($T_A = +25^\circ\text{C}$, unless otherwise noted)

Parameters / Test Conditions	Symbol	Min.	Max.	Unit
Gate-Source Breakdown Voltage $V_{DS} = 0, I_G = -1.0\mu\text{A dc}$ 2N4856, 2N4857, 2N4858 2N4859, 2N4860, 2N4861	$V_{(BR)GSS}$	-40 -30		Vdc
Gate-Source "Off" State Voltage $V_{DS} = 15\text{V dc}$ 2N4856, 2N4859 $I_D = 0.5\eta\text{A dc}$ 2N4857, 2N4860 2N4858, 2N4861	$V_{GS(off)}$	-4.0 -2.0 -0.8	-10 -6.0 -4.0	Vdc
Gate Reverse Current $V_{DS} = 0, V_{GS} = -20\text{V dc}$ 2N4856, 2N4857, 2N4858 $V_{DS} = 0, V_{GS} = -15\text{V dc}$ 2N4859, 2N4860, 2N4861	I_{GSS}		-0.25 -0.25	ηA
Drain Current Cutoff $V_{GS} = -10\text{V dc}, V_{DS} = 15\text{V dc}$	$I_{D(off)}$		0.25	ηA
Drain Current Zero Gate Voltage $V_{GS} = 0, V_{DS} = 15\text{V dc}$ 2N4856, 2N4859 2N4857, 2N4860 2N4858, 2N4861	I_{DSS}	50 20 8.0	175 100 80	mA
Drain-Source "On" State Voltage $V_{GS} = 0, I_D = 20\text{mA dc}$ 2N4856, 2N4859 $V_{GS} = 0, I_D = 10\text{mA dc}$ 2N4857, 2N4860 $V_{GS} = 0, I_D = 5.0\text{mA dc}$ 2N4858, 2N4861	$V_{DS(on)}$		0.75 0.50 0.50	Vdc
Static Drain - Source "On" State Resistance $V_{GS} = 0, I_D = 1.0\text{mA dc}$ 2N4856, 2N4859 2N4857, 2N4860 2N4858, 2N4861	$r_{ds(on)}$		25 40 60	Ω



TO-18
(TO-206AA)



6 Lake Street, Lawrence, MA 01841
1-800-446-1158 / (978) 620-2600 / Fax: (978) 689-0803
Website: <http://www.microsemi.com>

TECHNICAL DATA SHEET

N-CHANNEL J-FET Equivalent To MIL-PRF-19500/385

DYNAMIC CHARACTERISTICS

Parameters / Test Conditions	Symbol	Min.	Max.	Unit
Small-Signal, Common Short-Circuit Reverse Transfer Capacitance $V_{GS} = -10V$ dc, $V_{DS} = 0$, $f = 1.0MHz$ $C_1 = 0.1\mu F$, $L_1 = L_2 \geq 500\mu H$	C_{rss}		8.0	pF
Small-Signal, Common-Source Short-Circuit Input Capacitance $V_{GS} = -10V$ dc, $V_{DS} = 0$, $f = 1.0MHz$ $C_1 = 0.1\mu F$, $C_2 = 20.1\mu F$ $L_1 = L_2 \geq 500\mu H$	C_{iss}		18	pF

SWITCHING CHARACTERISTICS

Parameters / Test Conditions		Symbol	Min.	Max.	Unit
Turn-On Delay Time	2N4856, 2N4859 2N4857, 2N4860 2N4858, 2N4861	See Figure 3 of MIL-PRF-19500/385	$t_{d(on)}$	6 6 10	ηs
Rise Time	2N4856, 2N4859 2N4857, 2N4860 2N4858, 2N4861		t_r	3 4 10	ηs
Turn-Off Delay Time	2N4856, 2N4859 2N4857, 2N4860 2N4858, 2N4861		$t_{d(off)}$	25 50 100	ηs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Microchip:

[2N4859](#) [2N4857](#) [2N4856](#) [2N4860](#) [MV2N4856](#) [MV2N4857](#) [MV2N4858](#) [MV2N4859](#) [MV2N4860](#) [MV2N4861](#)
[MX2N4856](#) [MX2N4857](#) [MX2N4858](#) [MX2N4859](#) [MX2N4860](#) [MX2N4861](#)