



1 Amp Schottky Rectifier HSM150G, HSM160G



Dim.	Inches		Millimeter		Notes
	Minimum	Maximum	Minimum	Maximum	
A	.081	.087	2.06	2.21	
B	.160	.180	4.06	4.57	
C	.130	.155	3.30	3.94	
D	.077	.104	1.95	2.64	
E	.234	.256	5.95	6.50	



Microsemi
Catalog Number

HSM150
HSM160

Working
Peak Reverse
Voltage

50V
60V

Repetitive
Peak Reverse
Voltage

50V
60V

- Schottky Barrier Rectifier
- Guard Ring Protection
- 150°C Junction Temperature
- V_{RRM} 50 to 60 Volts

Electrical Characteristics

Average forward current
Maximum surge current
Max peak forward voltage
Max peak forward voltage
Max peak reverse current
Typical junction capacitance

$I_F(AV)$ 1.0 Amps
 I_{FSM} 50 Amps
 V_{FM} .51 Volts
 V_{FM} .69 Volts
 I_{RM} 100 μA
 C_J 53pF

Square wave
8.3ms, half sine, $T_J = 150^\circ C$
 $I_{FM} = 0.1A: T_J = 25^\circ C^*$
 $I_{FM} = 1.0A: T_J = 25^\circ C^*$
 $V_{RRM}, T_J = 25^\circ C$
 $V_R = 5.0V, T_J = 25^\circ C$

*Pulse test: Pulse width 300 μsec , Duty cycle 2%

Thermal and Mechanical Characteristics

Storage temperature range
Operating junction temp range
Maximum thermal resistance
Weight

T_{STG}
 T_J
 $R_{\theta JL}$

$-55^\circ C$ to $175^\circ C$
 $-55^\circ C$ to $175^\circ C$
25°C/W Junction to lead
.0047 ounces (.013 grams) typical



8700 East Thomas Road, P.O. Box 1390
Scottsdale, AZ 85252
PH: (480) 941-6300
FAX: (480) 947-1503
www.microsemi.com

05-11-07 Rev. 3

HSM150G, HSM160G

Figure 1
Typical Forward Characteristics




Figure 3
Typical Junction Capacitance





Figure 2
Typical Forward Characteristics





[ABOUT MICROSEMI](#) | [NEWS](#) | [CONTACTS](#) | [EMPLOYMENT](#) | [HOME](#)

keyword search:



part number search:



[Products](#)

[Sales Contacts](#)

[Support](#)

[Requests](#)

[Careers](#)

[Investors](#)

HSM160G/TR13 (#307478)



Schottky Rectifier

Division [CBU](#) Datasheet [HSM150G-60G.PDF](#)

Mil-Spec Spice Data (none)

Shipping (none) Qual Data Contact Microsemi

ROHS By Design

Description

1A,50V-60V surface mount Schottky rectifier in DO215AA gull wing package

Package
SMBG(SM)

[Privacy Policy](#) | [Site Map](#) | [Terms & Conditions](#)

[PPG Webex Portal](#) | [PPG Extranet Login](#)

[Avionics](#) | [Backlight Inverters](#) | [L-Band Radar](#) | [LED Driver](#) | [LDMOS & VDMOS](#) | [MOSFETs, IGBTs, & Diodes](#) | [Pin Diodes](#) | [Power Modules](#) | [RF Power & Bipolar Transistors](#) | [S-Band Radar](#) | [SCR](#) | [Thyristors](#) | [Varactor Diode](#) | [WLAN Power Amplifier](#) | [Zener Diode](#) | [Power Over Ethernet](#) | [IEEE802.3af](#) | [PoE ICs](#)

Copyright © 2011 Microsemi Corporation. All rights reserved. The Endwave logo is a registered trademark of Endwave Corporation.



[ABOUT MICROSEMI](#) | [NEWS](#) | [CONTACTS](#) | [EMPLOYMENT](#) | [HOME](#)

keyword
search:



part
number
search:



[Products](#)

[Sales Contacts](#)

[Support](#)

[Requests](#)

[Careers](#)

[Investors](#)

HSM160Ge3/TR13 (#307453)



Schottky Rectifier

Division [CBU](#) Datasheet [HSM150G-60G.PDF](#)

Mil-Spec Spice Data (none)

Shipping (none) Qual Data Contact Microsemi

ROHS By Design

Description

1A,50V-60V surface mount Schottky rectifier in DO215AA gull wing package

Package
SMBG(SM)

[Privacy Policy](#) | [Site Map](#) | [Terms & Conditions](#)

[PPG Webex Portal](#) | [PPG Extranet Login](#)

[Avionics](#) | [Backlight Inverters](#) | [L-Band Radar](#) | [LED Driver](#) | [LDMOS & VDMOS](#) | [MOSFETs, IGBTs, & Diodes](#) | [Pin Diodes](#) | [Power Modules](#) | [RF Power & Bipolar Transistors](#) | [S-Band Radar](#) | [SCR](#) | [Thyristors](#) | [Varactor Diode](#) | [WLAN Power Amplifier](#) | [Zener Diode](#) | [Power Over Ethernet](#) | [IEEE802.3af](#) | [PoE ICs](#)

Copyright © 2011 Microsemi Corporation. All rights reserved. The Endwave logo is a registered trademark of Endwave Corporation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microchip:](#)

[HSM160Ge3/TR13](#) [HSM160G/TR13](#)