P-Channel Enhancement-Mode Vertical DMOS FET

Features

- Free from secondary breakdown
- Low power drive requirement
- Ease of paralleling
- Low C_{ISS} and fast switching speeds
- High input impedance and high gain
- Excellent thermal stability
- Integral source-to-drain diode

Applications

- Motor controls
- Converters
- Amplifiers
- Switches
- Power supply circuits
- Drivers (relays, hammers, solenoids, lamps, memories, displays, bipolar transistors, etc.)

General Description

The Supertex VP3203 is an enhancement-mode (normally-off) transistor that utilizes a vertical DMOS structure and Supertex's well-proven silicon-gate manufacturing process. This combination produces a device with the power handling capabilities of bipolar transistors, and the high input impedance and positive temperature coefficient inherent in MOS devices. Characteristic of all MOS structures, this device is free from thermal runaway and thermally-induced secondary breakdown.

Supertex's vertical DMOS FETs are ideally suited to a wide range of switching and amplifying applications where very low threshold voltage, high breakdown voltage, high input impedance, low input capacitance, and fast switching speeds are desired.

Ordering Information

Device	Package Options			BV_{DSS}/BV_{DGS} (V)	$R_{DS(ON)}$ (max) (Ω)	$I_{D(ON)}$ (min) (A)
	TO-92	TO-243AA (SOT-89)	Die*			
VP3203	VP3203N3-G	VP3203N8-G	VP3203ND	-30	0.6	14.0

-G indicates package is RoHS compliant ('Green')
** Mil visual screening available.*

Absolute Maximum Ratings

Parameter	Value
Drain-to-source voltage	BV_{DSS}
Drain-to-gate voltage	BV_{DGS}
Gate-to-source voltage	±20V
Operating and storage temperature	-55°C to +150°C
Soldering temperature*	300°C

Absolute Maximum Ratings are those values beyond which damage to the device may occur. Functional operation under these conditions is not implied. Continuous operation of the device at the absolute rating level may affect device reliability. All voltages are referenced to device ground.

* *Distance of 1.6mm from case for 10 seconds.*

Pin Configurations



TO-92 (N3)



TO-243AA (SOT-89) (N8)

Product Marking

YY = Year Sealed
WW = Week Sealed
_____ = "Green" Packaging

Package may or may not include the following marks: Si or

TO-92 (N3)

W = Code for week sealed
_____ = "Green" Packaging

Packages may or may not include the following marks: Si or

TO-243AA (SOT-89) (N8)

Thermal Characteristics

Package	I_D (continuous)† (mA)	I_D (pulsed) (A)	Power Dissipation @T_A = 25°C (W)	θ_{jc} (°C/W)	θ_{ja} (°C/W)	I_{DR}† (mA)	I_{DRM} (A)
TO-92	-650	-4.0	0.74	125	170	-650	-4.0
TO-243AA (SOT-89)	-1100	-4.0	1.6‡	15	78‡	-1100	-4.0

† I_D (continuous) is limited by max rated T_j.
‡ Mounted on FR5 board, 25mm x 25mm x 1.57mm.

Electrical Characteristics (T_A = 25°C unless otherwise specified)

Sym	Parameter		Min	Typ	Max	Units	Conditions
BV_{DSS}	Drain-to-source breakdown voltage		-30	-	-	V	V_{GS} = 0V, I_D = -10mA
$V_{GS(th)}$	Gate threshold voltage		-1.0	-	-3.5	V	V_{GS} = V_{DS}, I_D= -10mA
$\Delta V_{GS(th)}$	Change in $V_{GS(th)}$ with temperature		-	-	-5.5	mV/°C	V_{GS} = V_{DS}, I_D= -10mA
I_{GSS}	Gate body leakage		-	-1.0	-100	nA	V_{GS} = ± 20V, V_{DS} = 0V
I_{DSS}	Zero gate voltage drain current		-	-	-10	µA	V_{GS} = 0V, V_{DS} = Max Rating
			-	-	-1.0	mA	V_{DS} = 0.8 Max Rating, V_{GS} = 0V, T_A = 125°C
$I_{D(ON)}$	On-state drain current		-	-14	-	A	V_{GS} = -10V, V_{DS} = -5.0V
$R_{DS(ON)}$	Static drain-to-source on-state resistance	TO-92	-	-	1.0	Ω	V_{GS} = -4.5V, I_D = -1.5A
		SOT-89	-	-	1.0		V_{GS} = -4.5V, I_D = -750mA
		TO-92	-	-	0.6		V_{GS} = -10V, I_D = -3.0A
		SOT-89	-	-	0.6		V_{GS} = -10V, I_D = -1.5A
$\Delta R_{DS(ON)}$	Change in $R_{DS(ON)}$ with temperature		-	-	1.0	%/°C	V_{GS} = -10V, I_D = -1.5A
G_{FS}	Forward transductance		1000	2000	-	mmho	V_{DS} = -25V, I_D = -2.0A
C_{ISS}	Input capacitance		-	200	300	pF	V_{GS} = 0V, V_{DS} = -25V, f = 1.0MHz
C_{OSS}	Common source output capacitance		-	100	120		
C_{RSS}	Reverse transfer capacitance		-	45	60		
$t_{d(ON)}$	Turn-on delay time		-	-	10	ns	V_{DD} = -25V, I_D = -2.0A, R_{GEN} = 10Ω
t_r	Rise time		-	-	15		
$t_{d(OFF)}$	Turn-off delay time		-	-	25		
t_f	Fall time		-	-	25		
V_{SD}	Diode forward voltage drop		-	-	-1.6	V	V_{GS} = 0V, I_{SD} = -1.5A
t_{rr}	Reverse recovery time		-	300	-	ns	V_{GS} = 0V, I_{SD} = -1.0A

Notes:
1. All D.C. parameters 100% tested at 25°C unless otherwise stated. (Pulse test: 300µs pulse, 2% duty cycle.)
2. All A.C. parameters sample tested.

Switching Waveforms and Test Circuit



Typical Performance Curves

Output Characteristics



Saturation Characteristics



Transconductance vs. Drain Current



Power Dissipation vs. Ambient Temperature



Maximum Rated Safe Operating Area



Thermal Response Characteristics



Typical Performance Curves *(cont.)*

BV_{DSS} Variation with Temperature



On-Resistance vs. Drain Current



Transfer Characteristics



$V_{(th)}$ and R_{DS} Variation with Temperature



Capacitance vs. Drain-to-Source Voltage



Gate Drive Dynamic Characteristics



3-Lead TO-92 Package Outline (N3)



Front View **Side View**



Bottom View

Symbol		A	b	c	D	E	E1	e	e1	L
Dimensions (inches)	MIN	.170	.014†	.014†	.175	.125	.080	.095	.045	.500
	NOM	-	-	-	-	-	-	-	-	-
	MAX	.210	.022†	.022†	.205	.165	.105	.105	.055	.610*

JEDEC Registration TO-92.
** This dimension is not specified in the JEDEC drawing.*
† This dimension differs from the JEDEC drawing.
Drawings not to scale.
***Supertex Doc.#:** DSPD-3TO92N3, Version E041009.*

3-Lead TO-243AA (SOT-89) Package Outline (N8)



Top View



Side View

Symbol		A	b	b1	C	D	D1	E	E1	e	e1	H	L
Dimensions (mm)	MIN	1.40	0.44	0.36	0.35	4.40	1.62	2.29	2.00†	1.50 BSC	3.00 BSC	3.94	0.89
	NOM	-	-	-	-	-	-	-	-			-	-
	MAX	1.60	0.56	0.48	0.44	4.60	1.83	2.60	2.29			4.25	1.20

JEDEC Registration TO-243, Variation AA, Issue C, July 1986.
† *This dimension differs from the JEDEC drawing*
Drawings not to scale.
Supertex Doc. #: *DSPD-3TO243AAN8, Version E051509.*

(The package drawing(s) in this data sheet may not reflect the most current specifications. For the latest package outline information go to http://www.supertex.com/packaging.html.)

Supertex inc.
1235 Bordeaux Drive, Sunnyvale, CA 94089
Tel: 408-222-8888
www.supertex.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Microchip:

VP3203N3-P014-G VP3203N3-P002-G VP3203N8-G VP3203N3-P013 VP3203N3-P003 VP3203N3-P014 VP3203N3-P002 VP3203N8 VP3203N3 VP3203N3-P013-G VP3203N3-G VP3203N3-P003-G VP3203N3-G P003 VP3203N3-G P002 VP3203N3-G P013 VP3203N3-G P005 VP3203N3-G P014