

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022281061

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK 254 Breakaway Header, Right-Angle with Friction Lock, 6 Circuits, 0.38µm Gold (Au) Selective Plating

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-10-07-001 (PDF)

Packaging Specification PK-40873-0056-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

Application tooling part link

|                               |            |
|-------------------------------|------------|
| Application Tooling Part Link | 11-20-1230 |
|-------------------------------|------------|


General

|                |                                 |
|----------------|---------------------------------|
| Product Family | PCB Headers                     |
| Series         | 42228                           |
| Application    | Signal, Wire-to-Board           |
| Overview       | KK® Interconnect System - Molex |
| Product Name   | KK 254                          |
| UPC            | 800753800748                    |

Physical

|                                |                           |
|--------------------------------|---------------------------|
| Breakaway                      | Yes                       |
| Circuits (Loaded)              | 6                         |
| Circuits (maximum)             | 6                         |
| Color - Resin                  | Black                     |
| Durability (mating cycles max) | 100                       |
| Flammability                   | 94V-0                     |
| Glow-Wire Capable              | No                        |
| Lock to Mating Part            | Yes                       |
| Material - Metal               | Brass                     |
| Material - Plating Mating      | Gold                      |
| Material - Plating Termination | Tin                       |
| Material - Resin               | Nylon                     |
| Net Weight                     | 0.867/g                   |
| Number of Rows                 | 1                         |
| Orientation                    | Right Angle               |
| PC Tail Length                 | 3.05mm                    |
| PCB Locator                    | No                        |
| PCB Retention                  | None                      |
| PCB Thickness - Recommended    | 1.60mm                    |
| Packaging Type                 | Bag                       |
| Pitch - Mating Interface       | 2.54mm                    |
| Plating min - Mating           | 0.381µm                   |
| Plating min - Termination      | 2.540µm                   |
| Polarized to Mating Part       | Yes                       |
| Polarized to PCB               | No                        |
| Shrouded                       | Partial                   |
| Stackable                      | No                        |
| Temperature Range - Operating  | See Product Specification |
| Termination Interface: Style   | Through Hole              |

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - ECHA\_01\_2020 (16 January 2020

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

42228 Series

Mates With

KK Crimp Housing [2695](#) , [6471](#) , [7880](#) , KK PC Board Connector [4455](#)

|                                                |                   |
|------------------------------------------------|-------------------|
| Current - Maximum per Contact                  | 4.0A              |
| Voltage - Maximum                              | 500V              |
| <b>Solder Process Data</b>                     |                   |
| Duration at Max. Process Temperature (seconds) | 005               |
| Lead-freeProcess Capability                    | WAVE              |
| Max. Cycles at Max. Process Temperature        | 001               |
| Process Temperature max. C                     | 235               |
| <b>Material Info</b>                           |                   |
| Engineering Number                             | 42228-0041        |
| <b>Reference - Drawing Numbers</b>             |                   |
| Packaging Specification                        | PK-40873-0056-001 |
| Product Specification                          | PS-10-07-001      |
| Sales Drawing                                  | SD-42228-001-001  |

This document was generated on 03/24/2020

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[22-28-1061](#)