

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022282237

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK 254 Breakaway Header, Right-Angle, with Plastic Polarizing Peg, 23 Circuits, Tin (Sn) Plating, with Backwalls Removed

Documents:

3D Model

Drawing (PDF)

Product Specification PS-10-07-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

42226

Application

Signal, Wire-to-Board

Application Tooling Part Link

11-20-1230

Comments

Backwalls Removed

Overview

KK® Interconnect System - Molex

Product Name

KK 254

UPC

800753811270

Physical

Breakaway

Yes

Circuits (Loaded)

23

Circuits (maximum)

23

Color - Resin

Black

Durability (mating cycles max)

25

Flammability

94V-0

Glow-Wire Capable

No

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

3.994/g

Number of Rows

1

Orientation

Right Angle

PC Tail Length

3.05mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

2.54mm

Plating min - Mating

2.540µm

Plating min - Termination

2.540µm

Polarized to Mating Part

No

Polarized to PCB

No

Shrouded

No

Stackable

No

Temperature Range - Operating

See Product Specification


Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

4.0A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free
Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

42226 Series

Mates With

KK Crimp Housing [2695](#) , [6471](#) , [7880](#) , KK
PC Board Connector [4455](#)

Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	42226-0233
Reference - Drawing Numbers	
Product Specification	PS-10-07-001
Sales Drawing	SD-42226-001, SD-42226-001-002

This document was generated on 09/18/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

22-28-2237