


MALE PCB PINS

PRINTED CIRCUIT PINS

5231

5231-0-00-XX-00-00-38-0


Swage mount in .094 hole
For a .125 thick board



9092

9092-0-00-XX-00-00-38-0


Wire crimp termination up to 14 AWG



7310

7310-0-01-XX-00-00-08-0


Board edge press-fit



5066

5066-0-00-26-00-00-03-0

Press-fit in .043 mounting hole




7937

7937-0-00-15-00-00-03-0

Target contact, horizontal surface mount
Also available on 16mm wide carrier tape:
2,400 parts per 13" reel.


See page 224.2 for Tape & Reel details




1502

1502-0-00-XX-00-00-03-0

Press-fit in .057 mounting hole




P.C.B. Layout




5102

5102-0-00-XX-00-00-33-0

Press-fit in .057 mounting hole



P.C.B. Layout




1508


1508-0-00-15-00-00-03-0

Test point, surface mount
Also available on 16mm wide carrier tape:
1,600 parts per 13" reel.

See page 224.2 for Tape & Reel details



P.C.B. Layout



SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Except swage pins which are annealed)

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$
Diameters: $\pm .002$
Angles: $\pm 2^\circ$

RoHS-2
2011/65/EU

ORDER CODE: XXXX - X - 0X - XX - 00 - 00 - XX - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- ◆ 80 200 μ " TIN OVER NICKEL (RoHS)
- ◆ 15 10 μ " GOLD OVER NICKEL (RoHS)
- ◆ 21 20 μ " GOLD OVER NICKEL (RoHS)
- ◆ 34 50 μ " GOLD OVER NICKEL (RoHS)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[7937-0-00-15-00-00-03-0](#) [1508-0-00-15-00-00-03-0](#) [1508-0-57-15-00-00-03-0](#) [7310-0-01-00-00-00-08-0](#) [1502-0-00-00-00-00-03-0](#) [5102-0-00-00-00-00-33-0](#)