



0326



0326-X-19-XX-06-XX-10-0
Swage mount in .060 hole


Basic Part Number	Board Thickness	Length V	Depth D
0326-1	.031	.062	.040
0326-2	.062	.094	.062
0326-3	.094	.125	.062
0326-4	.125	.156	.062

5295




5295-0-19-XX-06-XX-10-0
Solder mount in .086 min. mounting hole

0396



0396-0-15-XX-06-XX-10-0
Press-fit in .090 mounting hole


0298



0298-X-15-XX-06-XX-10-0
Swage mount in .060 hole


Basic Part Number	Board Thickness	Length V
0298-1	.031	.051
0298-2	.062	.082
0298-3	.094	.113
0298-4	.125	.145

9293




9293-0-15-XX-06-XX-10-0
Hex press-fit in .067 plated thru hole

8864



8864-0-15-XX-06-XX-10-0
Press-fit in .067 mounting hole

0664



0664-X-15-XX-06-XX-10-0
Swage mount in .096 hole

Basic Part Number	Board Thickness	Length V
0664-1	.094	.125
0664-2	.125	.156
0664-3	.188	.219

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 1X - XX - 06 - XX - 10 - 0

BASIC PART # _____

SPECIFY SHELL FINISH: _____

01 200μ" TIN/LEAD OVER NICKEL
15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH: _____

01 200μ" TIN/LEAD OVER NICKEL
14 10μ" GOLD OVER NICKEL
27 30μ" GOLD OVER NICKEL

CONTACT

#06 CONTACT (DATA ON PAGE 210)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0664-2-15-01-06-14-10-0](#) [0664-3-15-01-06-14-10-0](#) [0664-1-15-01-06-14-10-0](#) [0298-3-15-01-06-14-10-0](#) [0298-1-15-01-06-14-10-0](#) [0298-2-15-01-06-14-10-0](#) [0326-2-19-01-06-14-10-0](#) [0396-0-15-01-06-14-10-0](#) [0326-4-19-01-06-14-10-0](#) [0326-1-19-01-06-14-10-0](#) [0298-4-15-01-06-14-10-0](#) [0298-1-15-15-06-14-10-0](#) [0326-2-19-15-06-14-10-0](#) [0326-3-19-15-06-14-10-0](#) [0326-1-19-15-06-14-10-0](#) [0326-4-19-15-06-14-10-0](#)