

0512




0512-0-15-XX-12-XX-04-0
Press-fit in .057 mounting hole

0703




0703-0-15-XX-12-XX-04-0
Press-fit in .057 mounting hole

0574



0574-0-15-XX-12-XX-04-0
Press-fit in .057 mounting hole

0468




0468-0-15-XX-12-XX-04-0
Press-fit in .057 mounting hole

8894




8894-0-15-XX-12-XX-10-0
Hex press-fit in .059 plated thru hole

0550




0550-0-15-XX-22-XX-10-0
Solder mount in .052 min. mounting hole
Also available on 16mm wide carrier tape: 1,700 parts per 13" reel.
Order as: 0550-0-57-XX-22-XX-10-0

0671




0671-0-15-XX-12-XX-10-0
Solder mount in .063 min. mounting hole

0707



0707-0-15-XX-12-XX-10-0
Solder mount in .051 min. mounting hole

5739




5739-0-18-XX-12-XX-10-0
Surface mount
Also available on 16mm wide carrier tape: 3,000 parts per 13" reel.
Order as: 5739-0-58-XX-12-XX-10-0



P.C.B. Layout



1534



1534-X-15-XX-12-XX-04-0
Press-fit in .056 mounting hole

Basic Part Number	Length A
1534-0	.095
1534-1	.125

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: $\pm .005$
DIAMETERS: $\pm .002$
ANGLES: $\pm 2^\circ$

ORDER CODE: XXXX - X - 1X - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- 80 200 μ " TIN OVER NICKEL (RoHS)
- 15 10 μ " GOLD OVER NICKEL (RoHS)



SPECIFY CONTACT FINISH:

- 02 100 μ " TIN/LEAD OVER NICKEL
- 84 100 μ " TIN OVER NICKEL (RoHS)
- 27 30 μ " GOLD OVER NICKEL (RoHS)

SELECT CONTACT

#12 or #22 CONTACT (DATA ON PAGE 218)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0574-0-15-80-12-84-04-0](#) [0574-0-15-80-12-27-04-0](#) [0707-0-15-01-12-27-10-0](#) [0574-0-15-01-12-02-04-0](#) [0574-0-15-01-12-27-04-0](#) [0574-0-15-15-12-27-04-0](#)