


WRAPOST RECEPTACLES

FOR 0,38 - 0,64 DIAMETER PINS

1702/1703

170X-X-15-XX-30-XX-02-0

Press-fit in 1,45 mounting hole




Basic Part Number	# of Wraps	Length A
1702-2	2	9,4
1703-3	3	12,95

0038⇒0040/0066⇒0068

00XX-X-17-XX-30-XX-02-0

Press-fit in 1,45 mounting hole




Basic Part #	# of Wraps	Length A	Dia. C
0040-1	1	6,6	
0039-2	2	9,14	1,83
0038-3	3	12,7	
0068-1	1	6,6	
0067-2	2	9,14	1,57
0066-3	3	12,7	

0086/0088/0089

008X-X-17-XX-3X-XX-02-0

Press-fit in 1,45 mounting hole




Basic Part Number	# of Wraps	Length A
0089-2	2	9,4
0088-3	3	12,95
0086-4	4	16,0

1030⇒1036

103X-X-17-XX-3X-XX-02-0

Press-fit in 1,45 mounting hole




Basic Part #	# of Wraps	Length A	Dia. C
1032-1	1	6,6	
1031-2	2	9,14	1,83
1030-3	3	12,95	
1036-1	1	6,6	
1035-2	2	9,14	1,57
1034-3	3	12,95	

1045

1045-3-17-XX-30-XX-02-0


Press-fit in 1,09 mounting hole



1040

1040-3-17-XX-30-XX-02-0

Press-fit in 1,42 mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Millimeters

Tolerances On: Lengths: ± 0,13
Diameters: ± 0,051
Angles: ± 2°



ORDER CODE: XXXX - X - 17 - XX - XX - XX - 02 - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◆ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◆ 15 0,25µm GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 02 2,54µm TIN/LEAD OVER NICKEL
- ◆ 84 2,54µm TIN OVER NICKEL (RoHS)
- ◆ 27 0,76µm GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#30 or #32 CONTACT (DATA ON PAGE 253)

(For alternate contact choices, see groups B and C on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[1045-3-17-80-30-84-02-0](#) [1045-3-17-80-30-27-02-0](#) [1040-3-17-80-30-84-02-0](#) [1040-3-17-80-30-27-02-0](#) [1036-1-17-80-30-84-02-0](#) [1036-1-17-80-30-27-02-0](#) [1035-2-17-80-30-84-02-0](#) [1035-2-17-80-30-27-02-0](#) [1034-3-17-80-30-84-02-0](#) [1034-3-17-80-30-27-02-0](#) [1032-1-17-80-32-84-02-0](#) [1032-1-17-80-32-27-02-0](#) [1032-1-17-80-30-84-02-0](#) [1032-1-17-80-30-27-02-0](#) [1031-2-17-80-32-84-02-0](#) [1031-2-17-80-32-27-02-0](#) [1031-2-17-80-30-84-02-0](#) [1031-2-17-80-30-27-02-0](#) [1030-3-17-80-32-84-02-0](#) [1030-3-17-80-32-27-02-0](#) [1030-3-17-80-30-84-02-0](#) [1030-3-17-80-30-27-02-0](#) [0089-2-17-80-32-84-02-0](#) [0089-2-17-80-32-27-02-0](#) [0089-2-17-80-30-84-02-0](#) [0089-2-17-80-30-27-02-0](#) [0088-3-17-80-32-84-02-0](#) [0088-3-17-80-32-27-02-0](#) [0088-3-17-80-30-84-02-0](#) [0088-3-17-80-30-27-02-0](#) [0086-4-17-80-30-84-02-0](#) [0086-4-17-80-30-27-02-0](#) [0068-1-17-80-30-84-02-0](#) [0068-1-17-80-30-27-02-0](#) [0067-2-17-80-30-84-02-0](#) [0067-2-17-80-30-27-02-0](#) [0066-3-17-80-30-84-02-0](#) [0066-3-17-80-30-27-02-0](#) [0040-1-17-80-30-84-02-0](#) [0040-1-17-80-30-27-02-0](#) [0039-2-17-80-30-84-02-0](#) [0039-2-17-80-30-27-02-0](#) [0040-1-17-15-30-27-02-0](#) [1045-3-17-01-30-02-02-0](#) [1045-3-17-01-30-27-02-0](#) [1040-3-17-01-30-02-02-0](#) [1040-3-17-01-30-27-02-0](#) [1036-1-17-01-30-02-02-0](#) [1036-1-17-01-30-27-02-0](#) [1035-2-17-01-30-02-02-0](#) [1035-2-17-01-30-27-02-0](#) [1034-3-17-01-30-27-02-0](#) [1032-1-17-01-32-02-02-0](#) [1032-1-17-01-32-27-02-0](#) [1032-1-17-01-30-02-02-0](#) [1032-1-17-01-30-27-02-0](#) [1031-2-17-01-32-02-02-0](#) [1030-3-17-01-32-02-02-0](#) [1030-3-17-01-30-02-02-0](#) [0089-2-17-01-32-02-02-0](#) [0089-2-17-01-32-27-02-0](#) [0089-2-17-01-30-02-02-0](#) [0089-2-17-01-30-27-02-0](#) [0088-3-17-01-32-02-02-0](#) [0088-3-17-01-32-27-02-0](#) [0088-3-17-01-30-02-02-0](#) [0088-3-17-01-30-27-02-0](#) [0086-4-17-01-30-27-02-0](#) [0068-1-17-01-30-02-02-0](#) [0068-1-17-01-30-27-02-0](#) [0067-2-17-01-30-02-02-0](#) [0066-3-17-01-30-27-02-0](#) [0040-1-17-01-30-02-02-0](#) [0068-1-17-15-30-27-02-0](#) [0086-4-17-15-30-27-02-0](#) [0088-3-17-15-32-27-02-0](#) [0089-2-17-15-32-27-02-0](#) [1030-3-17-15-32-27-02-0](#) [1032-1-17-15-30-27-02-0](#) [1032-1-17-15-32-27-02-0](#) [1034-3-17-15-30-27-02-0](#) [1035-2-17-15-30-27-02-0](#) [1036-1-17-15-30-27-02-0](#) [1045-3-17-15-30-27-02-0](#)