


INTERCONNECTS

SERIES 800, 801, 830 • 2,54 GRID (0,76 DIA. PINS), SURFACE MOUNT HEADERS AND SOCKETS • SINGLE ROW STRIPS


Mates with Series 801...002 Surface Mount Z-Bend Socket (See Fig. 3)



Coplanarity 0,13. For pin counts >10 positions, consult Technical Support.

FIG. 1


Mates with Series 801...002 Surface Mount Z-Bend Socket (See Fig. 3)



Coplanarity 0,13. For pin counts >10 positions, consult Technical Support.

FIG. 2


Mates with Series 800...002 and 830...028 Surface Mount Header (See Fig. 1 & 2)



Coplanarity 0,13. For pin counts >10 positions, consult Technical Support.

FIG. 3

- Series 800 horizontal surface mount headers are available with 0,71 dia. pluggable pins (MM #1502). Series 830 horizontal surface mount z-bend headers use MM #3028 pins. See page 224 for details
- Series 801 horizontal surface mount Z-Bend sockets uses MM #1303 receptacles that accept pin diameters from 0,64 - 0,94 and 0,64 square leads. See pages 180 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- Ideal for daisy chaining parallel boards



ORDERING INFORMATION

FIG. 1	Series 800...002 0,71 Dia. Surface Mount Header	
	800-10-0-40-002000 Specify number of pins 02-10	
FIG. 2	Series 830...028 0,76 Dia. Surface Mount Z-Bend Header	
	830-XX-0-40-028000 Specify number of pins 02-10	
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264		
SPECIFY PLATING CODE XX=		
10		
40		
Pin Plating		
0,25µm Au		
5,08µm Sn		

FIG. 3	Series 801...002 0,71 Dia. Surface Mount Z-Bend Socket							
	801-XX-0-40-002000 Specify number of pins 02-10							
RoHS - 2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264								
SPECIFY PLATING CODE XX=			91	93	99	41	43	44
Sleeve (Pin)			5,08µm Sn/Pb	5,08µm Sn/Pb	5,08µm Sn/Pb	5,08µm Sn	5,08µm Sn	5,08µm Sn
Contact (Clip)			0,25µm Au	0,76µm Au	2,54µm Sn/Pb	0,25µm Au	0,76µm Au	2,54µm Sn



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[800-10-010-40-002000](#) [801-43-010-40-002000](#) [801-44-010-40-002000](#) [801-93-010-40-002000](#) [801-99-010-40-002000](#) [830-10-010-40-028000](#) [801-43-008-40-002000](#) [801-43-007-40-002000](#) [801-43-009-40-002000](#) [830-10-006-40-028000](#) [800-10-004-40-002000](#) [800-10-007-40-002000](#) [801-41-006-40-002000](#) [801-41-003-40-002000](#) [801-41-005-40-002000](#) [801-44-002-40-002000](#) [801-93-008-40-002000](#) [801-93-003-40-002000](#) [801-91-010-40-002000](#) [801-41-010-40-002000](#) [830-40-005-40-028000](#) [830-40-002-40-028000](#) [830-40-004-40-028000](#) [830-10-007-40-028000](#) [830-10-005-40-028000](#) [830-10-008-40-028000](#) [830-40-003-40-028000](#) [830-40-010-40-028000](#) [830-10-009-40-028000](#) [830-40-009-40-028000](#) [830-40-006-40-028000](#) [830-40-008-40-028000](#) [830-40-007-40-028000](#)