


MALE PCB PINS

SOLDER TERMINAL TURRETS

2111

2111-X-00-XX-00-00-07-0

Swage mount in .033 hole




Basic Part Number	Board Thickness	Length V
2111-1	.031	.053
2111-2	.062	.084
2111-3	.094	.115

2113

2113-X-00-XX-00-00-07-0

Swage mount in .043 hole




Basic Part Number	Board Thickness	Length V
2113-1	.031	.053
2113-2	.062	.084
2113-3	.094	.115
2113-4	.125	.147

2108

2108-X-00-XX-00-00-07-0

Swage mount in .043 hole




Basic Part Number	Board Thickness	Length V
2108-1	.031	.053
2108-2	.062	.084
2108-3	.094	.115
2108-4	.125	.147

2102

2102-X-00-XX-00-00-07-0

Swage mount in .052 hole




Basic Part Number	Board Thickness	Length V
2102-5	.016	.035
2102-1	.031	.054
2102-2	.062	.084
2102-3	.094	.115
2102-4	.125	.147

2109

2109-X-00-XX-00-00-07-0

Swage mount in .052 hole




Basic Part Number	Board Thickness	Length V
2109-1	.031	.052
2109-2	.062	.085

2324

2324-2-00-XX-00-00-07-0

Swage mount in .052 hole
For a .062 thick board



SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Swage pins are annealed)

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$
Diameters: $\pm .002$
Angles: $\pm 2^\circ$

RoHS-2
2011/65/EU

ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - 07 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- ◆ 80 200 μ " TIN OVER NICKEL (RoHS)
- ◆ 44 300 μ " SILVER OVER COPPER (RoHS)
- 50 300 μ " ELECTRO-SOLDER
(60/40 SnPb)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[2324-2-00-50-00-00-07-0](#) [2113-4-00-01-00-00-07-0](#) [2113-4-00-50-00-00-07-0](#) [2113-3-00-50-00-00-07-0](#) [2113-2-00-01-00-00-07-0](#) [2113-2-00-50-00-00-07-0](#) [2113-1-00-01-00-00-07-0](#) [2113-1-00-50-00-00-07-0](#) [2111-3-00-50-00-00-07-0](#) [2111-2-00-50-00-00-07-0](#) [2111-1-00-50-00-00-07-0](#) [2109-2-00-50-00-00-07-0](#) [2109-1-00-50-00-00-07-0](#) [2108-4-00-01-00-00-07-0](#) [2108-4-00-50-00-00-07-0](#) [2108-3-00-01-00-00-07-0](#) [2108-3-00-50-00-00-07-0](#) [2108-2-00-50-00-00-07-0](#) [2108-1-00-01-00-00-07-0](#) [2108-1-00-50-00-00-07-0](#) [2102-5-00-01-00-00-07-0](#) [2102-5-00-50-00-00-07-0](#) [2102-4-00-01-00-00-07-0](#) [2102-3-00-50-00-00-07-0](#) [2102-1-00-50-00-00-07-0](#) [2324-2-00-80-00-00-07-0](#) [2113-4-00-80-00-00-07-0](#) [2109-1-00-80-00-00-07-0](#) [2102-5-00-80-00-00-07-0](#) [2102-4-00-80-00-00-07-0](#) [2102-3-00-80-00-00-07-0](#) [2102-2-00-80-00-00-07-0](#) [2102-1-00-80-00-00-07-0](#) [2102-3-00-44-00-00-07-0](#) [2102-4-00-44-00-00-07-0](#) [2102-5-00-44-00-00-07-0](#) [2108-4-00-44-00-00-07-0](#) [2109-1-00-44-00-00-07-0](#) [2111-3-00-44-00-00-07-0](#) [2113-3-00-44-00-00-07-0](#) [2113-4-00-44-00-00-07-0](#) [2324-2-00-44-00-00-07-0](#)