


MALE PCB PINS

PRINTED CIRCUIT PINS

3408

3408-X-00-XX-00-00-03-0

Press-fit in 1,45 mounting hole




Basic Part Number	Pin Length A
3408-1	3,07
3408-2	4,60

0270/0282

02XX-0-01-XX-00-00-03-0

Press-fit in 1,45 mounting hole




Basic Part Number	Pin Material
0270-0	Phosphor Bronze 544
0282-0	Brass 360

0700

0700-0-00-XX-00-00-03-0


Press-fit in 1,45 mounting hole



8006

8006-0-00-XX-00-00-03-0


Press-fit in 0,86 mounting hole



0265

0265-0-01-XX-00-00-03-0


Press-fit in 1,45 mounting hole



0275

0275-0-01-XX-00-00-03-0


Press-fit in 1,45 mounting hole
Pin material is Phosphor Bronze 544 (B2)
For wire sizes up to 22 AWG



0272

0272-0-01-XX-00-00-03-0


Press-fit in 1,45 mounting hole



8000

8000-0-01-XX-00-00-03-0


Press-fit in 1,45 mounting hole
For wire sizes up to 22 AWG



3603

3603-0-07-XX-00-00-08-0


Annealed
Wire crimp termination. Accepts wire sizes 20 AWG Max. / 24 AWG Min.



9976

9976-0-00-XX-00-00-03-0

Press-fit in 0,97 mounting hole



SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Except where noted)

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 0X - XX - 00 - 00 - XX - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 15 0,25μm GOLD OVER NICKEL (RoHS)
- ◆ 21 0,51μm GOLD OVER NICKEL (RoHS)
- ◆ 34 1,27μm GOLD OVER NICKEL (RoHS)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[3408-2-00-01-00-00-03-0](#) [0270-0-01-80-00-00-03-0](#) [3408-2-00-80-00-00-03-0](#) [0265-0-01-21-00-00-03-0](#) [0270-0-01-21-00-00-03-0](#) [0270-0-01-34-00-00-03-0](#) [0272-0-01-21-00-00-03-0](#) [0275-0-01-21-00-00-03-0](#) [0282-0-01-15-00-00-03-0](#) [0282-0-01-21-00-00-03-0](#) [0282-0-01-34-00-00-03-0](#) [0700-0-00-15-00-00-03-0](#) [3408-1-00-15-00-00-03-0](#) [3408-1-00-34-00-00-03-0](#) [3408-2-00-15-00-00-03-0](#) [3408-2-00-21-00-00-03-0](#) [3408-2-00-34-00-00-03-0](#)