

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026481031

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 396 Breakaway Header, Vertical, 3 Circuits, Tin (Sn) Plating

Documents:

3D Model

Drawing (PDF)


Product Specification PS-08-50-001 (PDF)

Packaging Specification PK-41661-001-001 (PDF)

Symbol Footprint Data SYM-26-48-1031-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
Application tooling part link	
Application Tooling Part Link	11-20-0901
General	
Product Family	PCB Headers
Series	41661
Application	Board-to-Board, Power, Wire-to-Board
Overview	KK Interconnect Solutions
Product Name	KK 396
UPC	800753586956
Physical	
Breakaway	Yes
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	0.853/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	4.37mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

41661 Series

Mates With

2139 KK Crimp Housing, 41695 KK Crimp

Housing, 6442 KK Crimp Housing, 2145

PCB Connector, 41815 PCB Connector,

3069 KK Crimp Housing

Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	A-41661-A03A197
--------------------	-----------------

Reference - Drawing Numbers

Packaging Specification	PK-41661-001-001
Product Specification	PS-08-50-001
Sales Drawing	SD-41661-001-001, SD-41661-001-002
Symbol/Footprint Data	SYM-26-48-1031-001

This document was generated on 09/20/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[26-48-1031](#)