


MALE PCB PINS

SOLDER TERMINAL TURRETS

2501

2501-X-00-XX-00-00-07-0

Swage mount in 2,39 hole




Basic Part Number	Board Thickness	Length V
2501-1	0,79	1,98
2501-2	1,57	2,77
2501-3	2,39	3,56
2501-4	3,18	4,34

2703

2703-X-00-XX-00-00-07-0

Swage mount in 2,39 hole




Basic Part Number	Board Thickness	Length V
2703-1	0,79	1,96
2703-2	1,57	2,72
2703-3	2,39	3,48
2703-4	3,18	4,24

2702

2702-X-00-XX-00-00-07-0

Swage mount in 2,39 hole




Basic Part Number	Board Thickness	Length V	Depth D
2702-1	0,79	1,91	1,60
2702-2	1,57	2,67	2,36
2702-3	2,39	3,43	2,36
2702-4	3,18	4,19	2,36

2710

2710-X-00-XX-00-00-07-0

Swage mount in 2,39 hole




Basic Part Number	Board Thickness	Length V
2710-1	0,79	1,57
2710-2	1,57	2,39
2710-3	2,39	3,18
2710-4	3,18	3,96

2717

2717-X-00-XX-00-00-07-0


Swage mount in 2,39 hole



2713

2713-X-00-XX-00-00-07-0

Swage mount in 2,39 hole



Basic Part Number	Board Thickness	Length V
271X-1	0,79	1,57
271X-2	1,57	2,39
271X-3	2,39	3,18
271X-4	3,18	3,96

SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Swage pins are annealed)

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - 07 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 5,08μm TIN/LEAD OVER NICKEL
- ◆ 80 5,08μm TIN OVER NICKEL (RoHS)
- ◆ 44 7,62μm SILVER OVER COPPER (RoHS)
- 50 7,62μm ELECTRO-SOLDER (60/40 SnPb)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[2717-4-00-01-00-00-07-0](#) [2717-4-00-50-00-00-07-0](#) [2717-3-00-01-00-00-07-0](#) [2717-3-00-50-00-00-07-0](#) [2717-2-00-01-00-00-07-0](#) [2717-2-00-50-00-00-07-0](#) [2717-1-00-50-00-00-07-0](#) [2713-4-00-01-00-00-07-0](#) [2713-4-00-50-00-00-07-0](#) [2713-3-00-01-00-00-07-0](#) [2713-3-00-50-00-00-07-0](#) [2713-2-00-01-00-00-07-0](#) [2713-2-00-50-00-00-07-0](#) [2713-1-00-01-00-00-07-0](#) [2713-1-00-50-00-00-07-0](#) [2710-4-00-50-00-00-07-0](#) [2710-3-00-01-00-00-07-0](#) [2710-3-00-50-00-00-07-0](#) [2710-2-00-01-00-00-07-0](#) [2710-2-00-50-00-00-07-0](#) [2710-1-00-50-00-00-07-0](#) [2703-4-00-01-00-00-07-0](#) [2703-4-00-50-00-00-07-0](#) [2703-3-00-01-00-00-07-0](#) [2703-3-00-50-00-00-07-0](#) [2703-2-00-01-00-00-07-0](#) [2703-1-00-01-00-00-07-0](#) [2703-1-00-50-00-00-07-0](#) [2702-4-00-01-00-00-07-0](#) [2702-4-00-50-00-00-07-0](#) [2702-3-00-01-00-00-07-0](#) [2702-3-00-50-00-00-07-0](#) [2702-2-00-50-00-00-07-0](#) [2702-1-00-01-00-00-07-0](#) [2702-1-00-50-00-00-07-0](#) [2501-4-00-50-00-00-07-0](#) [2501-3-00-50-00-00-07-0](#) [2501-2-00-50-00-00-07-0](#) [2501-1-00-50-00-00-07-0](#) [2717-4-00-80-00-00-07-0](#) [2717-3-00-80-00-00-07-0](#) [2717-2-00-80-00-00-07-0](#) [2717-1-00-80-00-00-07-0](#) [2713-4-00-80-00-00-07-0](#) [2713-3-00-80-00-00-07-0](#) [2713-2-00-80-00-00-07-0](#) [2713-1-00-80-00-00-07-0](#) [2710-4-00-80-00-00-07-0](#) [2710-2-00-80-00-00-07-0](#) [2710-1-00-80-00-00-07-0](#) [2703-4-00-80-00-00-07-0](#) [2703-3-00-80-00-00-07-0](#) [2703-2-00-80-00-00-07-0](#) [2703-1-00-80-00-00-07-0](#) [2702-4-00-80-00-00-07-0](#) [2702-3-00-80-00-00-07-0](#) [2702-2-00-80-00-00-07-0](#) [2501-3-00-44-00-00-07-0](#) [2501-4-00-44-00-00-07-0](#) [2702-1-00-44-00-00-07-0](#) [2702-3-00-44-00-00-07-0](#) [2702-4-00-44-00-00-07-0](#) [2703-2-00-44-00-00-07-0](#) [2703-3-00-44-00-00-07-0](#) [2703-4-00-44-00-00-07-0](#) [2710-1-00-44-00-00-07-0](#) [2710-3-00-44-00-00-07-0](#) [2710-4-00-44-00-00-07-0](#) [2713-1-00-44-00-00-07-0](#) [2713-2-00-44-00-00-07-0](#) [2713-3-00-44-00-00-07-0](#) [2713-4-00-44-00-00-07-0](#) [2717-1-00-44-00-00-07-0](#) [2717-2-00-44-00-00-07-0](#) [2717-3-00-44-00-00-07-0](#) [2717-4-00-44-00-00-07-0](#)