

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026481102

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 396 Breakaway Header, Right-Angle, 10 Circuits, Tin (Sn) Plating

Documents:	
3D Model	Packaging Specification PK-41662-001-001 (PDF)
Drawing (PDF)	Symbol Footprint Data SYM-26-48-1102-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-08-50-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

Application tooling part link


Application Tooling Part Link	11-20-0901
-------------------------------	------------

General

Product Family	PCB Headers
Series	41662
Application	Board-to-Board, Power, Wire-to-Board
Overview	KK Interconnect Solutions
Product Name	KK 396
UPC	800754384537

Physical

Breakaway	Yes
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	3.838/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	4.67mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Partial



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[41662](#) Series

Mates With

[2139](#) KK Crimp Housing, [41695](#) KK Crimp Housing, [6442](#) KK Crimp Housing, [2145](#) PCB Connector, [41815](#) PCB Connector, [3069](#) KK Crimp Housing

Stackable	No
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	7.0A
Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	A-41662-B10A197
Reference - Drawing Numbers	
Packaging Specification	PK-41662-001-001
Product Specification	PS-08-50-001
Sales Drawing	SD-41662-001-001, SD-41662-001-002
Symbol/Footprint Data	SYM-26-48-1102-001

This document was generated on 11/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[26-48-1102](#)