

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026580060

Status:

Active

Overview:

Description:

KK 396 Breakaway Header, Vertical, 6 Circuits, Tin (Sn) Plating, Pin length 26.21mm (1.032")

Agency Certification		
CSA		LR19980
UL		E29179
Application tooling part link		
Application Tooling Part Link		11-20-0901
General		
Product Family		PCB Headers
Series		41661
Application		Board-to-Board, Signal, Wire-to-Board
Overview		kk_interconnect_solutions
Product Name		KK 396
UPC		800754915144
Physical		
Breakaway		Yes
Circuits (Loaded)		6
Circuits (maximum)		6
Color - Resin		Black
Durability (mating cycles max)		25
First Mate / Last Break		No
Flammability		94V-0
Glow-Wire Capable		No
Guide to Mating Part		No
Keying to Mating Part		None
Lock to Mating Part		None
Material - Metal		Brass
Material - Plating Mating		Tin
Material - Plating Termination		Tin
Material - Resin		Polyester
Net Weight		2.191/g
Number of Rows		1
Orientation		Vertical
PC Tail Length		3.56mm
PCB Locator		No
PCB Retention		None
PCB Thickness - Recommended		1.60mm
Packaging Type		Bag
Pitch - Mating Interface		3.96mm
Pitch - Termination Interface		3.96mm
Polarized to Mating Part		No
Polarized to PCB		No
Shrouded		No
Stackable		Yes
Surface Mount Compatible (SMC)		No
Temperature Range - Operating		See Product Specification
Termination Interface: Style		Through Hole
Electrical		
Current - Maximum per Contact		4.5A
Voltage - Maximum		250V

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

41661 Series

Mates With

2139 KK Crimp Housing, 41695 KK Crimp Housing, 6442 KK Crimp Housing, 2145 PCB Connector, 41815 PCB Connector, 3069 KK Crimp Housing

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	A-41661-A06Y197
--------------------	-----------------

Reference - Drawing Numbers

Packaging Specification	PK-41661-001-001
Product Specification	PS-08-50-001
Sales Drawing	SD-41661-001-001, SD-41661-001-002
Symbol/Footprint Data	SYM-26-48-1061-001

This document was generated on 09/20/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[26-58-0060](#)